



$A_0 \pm 0.1$	$B_0 \pm 0.1$	$K_0 \pm 0.1$	$K_i \pm 0.1$	$E \pm 0.10$	$F \pm 0.1$	$P_0 \pm 0.1$	$P_1 \pm 0.1$	$P_2 \pm 0.1$	$D_0 + 0.1$	$D_1 + 0.1$	$T \pm 0.05$	$S_0 \pm 0.1$	$W \pm 0.3$
14.2	22.5	3.2	2.1	1.75	20.2	4.0	16.0	2.0	$\phi 1.5$	$\phi 2.0$	0.30	40.4	44.0

TOLERANCES UNLESS OTHERWISE SPECIFIED
 DECIMAL 25
 X ± .25
 XX ± .12
 XXX ± .12

APPROVALS _____ DATE _____

ANGLE ±.5°

IDT
 www.IDT.com
 6024 Silver Creek Valley Road,
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-3572

TITLE: BG/BGC 119 CARRIER TAPE

SCALE: N/A

STOCK NO. N/A

DRAWING NO. MSC-3411-A

REV 00

DO NOT SCALE DRAWING SHEET 1 OF 1