



$A_0 \pm 0.10$	$A_1 \pm 0.1$	$B_0 \pm 0.10$	$B_1 \pm 0.1$	$K_0 \pm 0.1$	$K_1 \pm 0.1$	$E \pm 0.10$	$F \pm 0.1$	$P_0 \pm 0.1$	$P_1 \pm 0.1$	$P_2 \pm 0.1$	$D_0 + 0.1$	$D_1 + 0.1$	$T \pm 0.05$	$S_0 \pm 0.1$	$W \pm 0.3$
23.3	23.5	23.3	23.5	3.57	2.57	1.75	20.2	4.0	32.0	2.0	$\phi 1.5$	$\phi 2.0$	0.30	40.4	44.0

TOLERANCES UNLESS OTHERWISE SPECIFIED
 DECIMAL 25
 X ± .25
 .XX ± .13
 .XXX ± .13

ANGLE
 F.5°



6024 Silver Creek Valley Road,
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-3572

WWW.IDT.COM

APPROVALS

DATE

DRAWN

TITLE:
 BL/BLG/BR/HL/HLG 484
 CARRIER TAPE

SCALE
 N/A

STOCK NO.

DRAWING NO.
 MSC-5731-A

REV
 00

SIZE

DO NOT SCALE DRAWING

SHEET 1 OF 1