



$A_0 \pm 0.10$	$B_0 \pm 0.10$	$K_0 \pm 0.1$	$K_i \pm 0.1$	$E \pm 0.10$	$F \pm 0.1$	$P_0 \pm 0.1$	$P_1 \pm 0.1$	$P_2 \pm 0.1$	$D_0 + 0.1$	$D_1 + 0.1$	$T \pm 0.05$	$S_0 \pm 0.1$	$W \pm 0.3$
23.3	23.3	2.11	1.25	1.75	20.2	4.0	32.0	2.0	$\phi 1.5$	$\phi 2.0$	0.30	40.4	44.0

TOLERANCES UNLESS OTHERWISE SPECIFIED  
 DECIMAL 25  
 X ± .25  
 XX ± .13  
 XXX ± .13

ANGLE  
 ±.5°

APPROVALS DATE

**IDT**  
 www.IDT.com

6024 Silver Creek Valley Road,  
 San Jose, CA 95138  
 PHONE: (408) 284-8200  
 FAX: (408) 284-3572

TITLE: BX/BXG 288 CARRIER TAPE		SCALE N/A	
STOCK NO. N/A	DRAWING NO. MSC-5761-A	REV 00	SIZE
DO NOT SCALE DRAWING		SHEET 1 OF 1	