



Ao ±0.1	Bo ±0.1	Ko ±0.1	Ki ±0.1	F ±0.1	P1 ±0.1	D1 +0.1	So +0.1	W ±0.3
17.2	17.2	2.0	1.4	14.2	24.0	2.0	28.4	32.0

TOLERANCES UNLESS OTHERWISE SPECIFIED  
 DECIMAL .XX ± .13  
 .XXX ± .13  
 ANGLE ±.5°

**IDT**  
 6024 Silver Creek Valley Road,  
 San Jose, CA 95138  
 PHONE: (408) 284-8200  
 FAX: (408) 284-5572

WWW.IDT.COM

TITLE: DQ/DDG 100, EQ/EOG 100 & PN/PNG  
 64/80/100/120/128 CARRIER TAPE

STOCK NO. N/A  
 DRAWING NO. MSC-3389-A  
 REV 00

SCALE N/A  
 SIZE

DO NOT SCALE DRAWING SHEET 1 OF 1