



| | | | | | | | | | | | | |
|---------------|---------------|---------------|---------------|-------------|-------------|---------------|---------------|---------------|-------------|-------------|--------------|-------------|
| $A_0 \pm 0.1$ | $B_0 \pm 0.1$ | $K_0 \pm 0.1$ | $K_i \pm 0.1$ | $E \pm 0.1$ | $F \pm 0.1$ | $P_0 \pm 0.1$ | $P_1 \pm 0.1$ | $P_2 \pm 0.1$ | $D_0 + 0.1$ | $D_1 + 0.1$ | $T \pm 0.05$ | $W \pm 0.3$ |
| 8.5 | 8.5 | 1.6 | 1.3 | 1.75 | 7.5 | 4.0 | 12.0 | 2.0 | $\phi 1.5$ | $\phi 1.5$ | 0.30 | 16.0 |

TOLERANCES UNLESS OTHERWISE SPECIFIED
 DECIMALS .25
 .X \pm .13
 .XX \pm .13
 .XXX \pm .13

ANGLE \pm .5°

DATE 11/19/07

APPROVALS

WWW.IDT.COM

6024 Silver Creek Valley Road
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-3572



TITLE: LL/LLG 124, ND/NDG 68 & NL/NLG 52/56 CARRIER TAPE

| | | | |
|----------------|----------|----------------------|--------------|
| DRAWN | 11/19/07 | SCALE | N/A |
| CHECKED | | SIZE | B |
| STOCK NO. | N/A | DRAWING NO. | MSC-3450-A |
| REV | | REV | 00 |
| FILE: MSC17011 | | DO NOT SCALE DRAWING | SHEET 1 OF 1 |