



A0 ±0.1	Bo ±0.1	Ko ±0.1	Ki ±0.1	E ±0.1	F ±0.1	PO ±0.1	P1 ±0.1	P2 ±0.1	Do +0.1	D1 +0.1	T ±0.05	W ±0.3
7.3	7.3	1.5	1.2	1.75	7.5	4.0	12.0	2.0	ø1.5	ø1.5	0.30	16.0

TOLERANCES UNLESS OTHERWISE SPECIFIED
 DECIMAL .25
 .XX ± .13
 .XXX ± .13
 ANGLE ±.5°
 WWW.IDT.COM
 6024 Silver Creek Valley Road,
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-5972



TITLE:	NB/NBG 48, ND/NDG 56 & NL/NLG 48 CARRIER TAPE	
STOCK NO.	N/A	DRAWING NO. MSC-7353-A
SCALE	N/A	REV 00
DRAWN		DATE
APPROVALS		DATE
DO NOT SCALE DRAWING SHEET 1 OF 1		