



SECTION Y-Y

Ao	2.30	+/-0.1
Bo	3.20	+/-0.1
Ko	1.00	+/-0.1
F	3.50	+/-0.05
P1	4.00	+/-0.1
W	8.00	+/-0.3

TOLERANCES UNLESS OTHERWISE SPECIFIED
 DECIMAL 25
 X ± .25
 Y ± .13
 XXX ± .13
 ANGLE ±.5°
 APPROVALS DATE

IDT
 6024 Silver Creek Valley Road,
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-3572
 www.IDT.com

TITLE:
 NC/NCG 8 & NR/NRG 8
 CARRIER TAPE

STOCK NO. N/A
 DRAWING NO. MSC-5940-A
 DO NOT SCALE DRAWING SHEET 1 OF 1

SCALE
 N/A
 SIZE

REV
 00