



A0 ±0.1	B0 ±0.1	K0 ±0.1	Ki ±0.1	E ±0.1	F ±0.1	P0 ±0.1	P1 ±0.1	P2 ±0.1	D0 +0.1	D1 +0.1	T ±0.05	W ±0.3
4.3	7.8	1.05	NA	1.75	7.5	4.0	8.0	2.0	ø1.5	ø1.5	0.30	16.0

TOLERANCES UNLESS OTHERWISE SPECIFIED
 DECIMAL 25
 X ±.25
 Y ±.15
 XXX ±.13
 APPROVALS _____ DATE _____
IDT
 www.IDT.com
 6024 Silver Creek Valley Road,
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-3572

TITLE: NR/NRG 36 CARRIER TAPE		SCALE N/A
STOCK NO. N/A	DRAWING NO. MSC-7025-A	REV 00
DO NOT SCALE DRAWING		SHEET 1 OF 1