

HS-4423RH, HS-4423EH, HS-4423BRH, HS-4423BEH

Radiation Hardened Dual, Inverting Power MOSFET Drivers

FN4564

Rev 5.00

February 11, 2014

The Radiation Hardened HS-4423RH, HS-4423EH, HS-4423BRH, HS-4423BEH are inverting, dual, monolithic high-speed MOSFET drivers designed to convert TTL level signals into high current outputs at voltages up to 18V.

The inputs of these devices are TTL compatible and can be directly driven by our HS-1825ARH PWM device or by our ACS/ACTS and HCS/HCTS type logic devices. The fast rise times and high current outputs allow very quick control of high gate capacitance power MOSFETs in high frequency applications.

The high current outputs minimize power losses in MOSFETs by rapidly charging and discharging the gate capacitance. The output stage incorporates a low voltage lock-out circuit that puts the outputs into a three-state mode when the supply voltage drops below 10V for the HS-4423RH, HS-4423EH and 7.5V for the HS-4423BRH and HS-4423BEH.

Constructed with the Intersil dielectrically isolated Rad Hard Silicon Gate (RSG) BiCMOS process, these devices are immune to Single Event Latch-up and have been specifically designed to provide highly reliable performance in harsh radiation environments

Features


- Electrically screened to DLA SMD # [5962-99511](#)
- QML qualified per MIL-PRF-38535 requirements
- EH version acceptance tested to 50krad(Si) (LDR)
- Radiation environment
 - High dose rate (50-300rad(Si)/s) 300krad(Si)
 - Latch-up immune
 - Low dose rate immune
- I_{PEAK} >2A (typ)
- Matched rise and fall times (C_L = 4300pF) 75ns (max)
- Low voltage lock-out feature
 - HS-4423RH, HS-4423EH, <10.0V
 - HS-4423BRH, HS-4423BEH <7.5V
- Wide supply voltage range 12V to 18V
- Prop delay 250ns (max)
- Consistent delay times with V_{CC} changes
- Low power consumption
 - 40mW with inputs high
 - 20mW with inputs low
- Low equivalent input capacitance 3.2pF (typ)
- ESD protected 4000V

Applications

- Switching power supplies
- DC/DC converters
- Motor controllers

Pin Configuration

HS-4423RH, HS-4423EH, HS-4423BRH, HS-4423BEH
(FLATPACK CDFP4-F16)



NOTE: Pins 4 and 5, 10 and 11, 12 and 13, 14 and 15 are double-bonded to their same electrical points on the die.

Ordering Information

ORDERING SMD NUMBER (Note 2)	PART NUMBER (Note 1)	TEMPERATURE RANGE (°C)	PACKAGE (RoHS Compliant)	PKG. DWG. #
5962F9951101VXC	HS9-4423RH-Q	-55 to +125	16 Ld Flatpack	K16.A
5962F9951101QXC	HS9-4423RH-8	-55 to +125	16 Ld Flatpack	K16.A
HS9-4423RH/PROTO	HS9-4423RH/PROTO	-55 to +125	16 Ld Flatpack	K16.A
5962F9951102VXC	HS9-4423BRH-Q	-55 to +125	16 Ld Flatpack	K16.A
5962F9951102QXC	HS9-4423BRH-8	-55 to +125	16 Ld Flatpack	K16.A
5962F9951103VXC	HS9-4423EH-Q	-55 to +125	16 Ld Flatpack	K16.A
5962F9951104VXC	HS9-4423BEH-Q	-55 to +125	16 Ld Flatpack	K16.A
HS9-4423BRH/PROTO	HS9-4423BRH/PROTO	-55 to +125	16 Ld Flatpack	K16.A
5962F9951101V9A	HS0-4423RH-Q	-55 to +125	Die	
5962F9951103V9A	HS0-4423EH-Q	-55 to +125	Die	

NOTES:

1. These Intersil Pb-free Hermetic packaged products employ 100% Au plate - e4 termination finish, which is RoHS compliant and compatible with both SnPb and Pb-free soldering operations.
2. Specifications for Rad Hard QML devices are controlled by the Defense Logistics Agency Land and Maritime (DLA). The SMD numbers listed in the "Ordering Information" table must be used when ordering.

© Copyright Intersil Americas LLC 2002-2014. All Rights Reserved.
All trademarks and registered trademarks are the property of their respective owners.

For additional products, see www.intersil.com/en/products.html

Intersil products are manufactured, assembled and tested utilizing ISO9001 quality systems as noted in the quality certifications found at www.intersil.com/en/support/qualandreliability.html

Intersil products are sold by description only. Intersil may modify the circuit design and/or specifications of products at any time without notice, provided that such modification does not, in Intersil's sole judgment, affect the form, fit or function of the product. Accordingly, the reader is cautioned to verify that datasheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.

For information regarding Intersil Corporation and its products, see www.intersil.com

Die Characteristics

DIE DIMENSIONS:

4890 μ m x 3370 μ m (193 mils x 133 mils)
Thickness: 483 μ m \pm 25.4 μ m (19 mils \pm 1 mil)

INTERFACE MATERIALS:

Glassivation:

Type: PSG (Phosphorous Silicon Glass)
Thickness: 8.0k Å \pm 1.0k Å

Top Metallization:

Type: AlSiCu
Thickness: 16.0k Å \pm 2k Å

Substrate:

Radiation Hardened Silicon Gate,
Dielectric Isolation

Backside Finish:

Silicon

ASSEMBLY RELATED INFORMATION:

Substrate Potential:

Unbiased (DI)

ADDITIONAL INFORMATION:

Worst Case Current Density:

$<2.0 \times 10^5$ A/cm²

Transistor Count:

125

Metallization Mask Layout

HS-4423RH, HS-4423EH, HS-4423BRH, HS-4423BEH

