

Product	Version
Renesas Flash Programmer V3	V3.24.00

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

Microcontroller	Group	Product Name	Serial	USB	E1/E20	E2 Lite	E2	J-Link	Select Product Name	Additional information
Power Management	Battery Management	RAJ240071	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Power Management	Battery Management	RAJ240075	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Power Management	Battery Management	RAJ240080	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Power Management	Battery Management	RAJ240090	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Power Management	Battery Management	RAJ240091	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Power Management	Battery Management	RAJ240100	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Power Management	Battery Management	RAJ240310	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Power Management	Battery Management	RAJ240500	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Power Management	Battery Management	RAJ242095	-	-	-	✓ (SWD)	✓ (SWD)	✓ (SWD)	RA	
Renesas USB Power Delivery	C30	R9A02G011	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Renesas USB Power Delivery	C30	R9J02G012	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Renesas USB Power Delivery	C30	R9A02G0150	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
Renesas USB Power Delivery	C30	R9A02G0151	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	
ICs for Motor Driver/Actuator Driver	ICs for Motor Control	RAJ306000	1 wire UART(TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	-	RL78	