

---

**Option List      HD6432144S,HD6432143S,HD6432134S,HD6432133S**


---

Please check off the appropriate applications by  ,  or  within  and enter the necessary information.

**(1) ROM size**

<input type="checkbox"/>	HD6432144S	:	128-kbytes
<input type="checkbox"/>	HD6432143S	:	96-kbytes
<input type="checkbox"/>	HD6432134S	:	128-kbytes
<input type="checkbox"/>	HD6432133S	:	96-kbytes

Date of order	
Customer	
Department	
Name	
ROM code Name	
LSI number (Renesas entry)	

**(2) System Oscillator**

<input type="checkbox"/>	Crystal oscillator	f =		MHz
<input type="checkbox"/>	External clock	f =		MHz

**(3) Power Supply Voltage/Maximum Operating Frequency**

<input type="checkbox"/>	Vcc = 4.5V to 5.5V (20 MHz max.)
<input type="checkbox"/>	Vcc = 4.0V to 5.5V (16 MHz max.)

- Notes:
1. Please select the power supply voltage/operating frequency version according to the power supply voltage used.  
Example: For use at Vcc = 4.5V to 5.5V/f = 10MHz  
select Vcc = 4.5V to 5.5V(20MHz max.).
  2. The power supply voltage and maximum operating frequency of the selected version should also be entered on the Single-Chip Microcomputer Ordering Specifications sheet.