

Option List HD6432237,HD6432235,HD6432233

Please check off the appropriate application:
by , or within and enter the
necessary information

(1) ROM size

<input type="checkbox"/> HD6432237,HD6432235	:128-kbytes
<input type="checkbox"/> HD6432233	:64-kbytes

(2) RAM size

<input type="checkbox"/> HD6432237	:16-kbytes
<input type="checkbox"/> HD6432235,HD6432233	:4-kbytes

(3) System Oscillator(OSC1,OSC2)

<input type="checkbox"/> Crystal oscillator	f =	MHz
<input type="checkbox"/> External clock	f =	MHz

(4) Power Supply Voltage/Maximum Operating Frequency, [Watch Mode Operating Voltage/Frequency]

<input type="checkbox"/>	Vcc = 2.7V to 3.6V / 13.5MHz max, [Vcc = 2.7V to 3.6V / 32kHz] for HD6432237,HD6432235,HD6432233
<input type="checkbox"/>	Vcc = 2.7V to 3.6V / 13.5MHz max, [Vcc = 2.2V to 3.6V / 32kHz] for HD6432237,HD6432235,HD6432233
<input type="checkbox"/>	Vcc = 2.2V to 3.6V / 6.25MHz max, [Vcc = 2.2 V to 3.6V / 32kHz] for HD6432237,HD6432235,HD6432233

Notes: 1.Please select the power supply voltage/operating frequency version according to the power supply voltage used.

Example: For use at Vcc = 2.7V to 3.6V / f = 6MHz

select Vcc = 2.7V to 3.6V / f = 13.5MHz max.

2.The power supply voltage and maximum operating frequency of the selected version should also be entered on the Single-Chip Microcomputer Ordering Specifications sheet.

Date of order	
Customer	
Department	
Name	
ROM code Name	
LSI number (RENESAS entry)	