

**Option List      HD6433397,HD6433396,HD6433394**

Please check off the appropriate applications by  ,  or  within  and enter the necessary information.

## (1) ROM size

<input type="checkbox"/>	HD6433394	:	32-kbytes
<input type="checkbox"/>	HD6433396	:	48-kbytes
<input type="checkbox"/>	HD6433397	:	60-kbytes

## (2) System Oscillator(OSC1,OSC2)

<input type="checkbox"/>	Crystal oscillator	f =		MHz
<input type="checkbox"/>	External clock	f =		MHz

## (3) Power Supply Voltage / Maximum Operating Frequency

<input type="checkbox"/>	Vcc = 4.5V to 5.5V (16 MHz max.)
<input type="checkbox"/>	Vcc = 4.0V to 5.5V (12 MHz max.)
<input type="checkbox"/>	Vcc = 2.7V to 5.5V (10 MHz max.)

Date of order	
Customer	
Department	
Name	
ROM code Name	
LSI number (Renesas entry)	

**Notes: 1.Please select the power supply voltage/operating frequency version according to the power supply voltage used.**

**Example: For use at Vcc = 4.5V to 5.5V/f = 10MHz  
select Vcc = 4.5V to 5.5V(16MHz max.).**

**2.The power supply voltage and maximum operating frequency of the selected version should also be entered on the Single-Chip Microcomputer Ordering Specifications sheet.**