## Old Company Name in Catalogs and Other Documents

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <a href="http://www.renesas.com">http://www.renesas.com</a>

April 1<sup>st</sup>, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<a href="http://www.renesas.com">http://www.renesas.com</a>)

Send any inquiries to http://www.renesas.com/inquiry.



RI	EJ19B067	1-0100					Ma	ask R	OM number	
			MASK ROM ORDER CON			M	Ī		Date:	
	SINGLE-CHIP MICROCOMPUTER M34524MC-XXXFP RENESAS TECHNOLOGY						Ħ.	Section head signature	Supervisor signature	
	Please fi	ll in all ite	ms marked **.					Receipt		
*	Customer	Company name					Responsible	Supervisor		
			TEL (			)	nce	nce ture		
		Date issued	Date:				Issuance	signature		
*		sets of EF	PROMs are required for each is required for each pattern	•					•	ROMs.
	Specif If at le masks on the	east two of based on products	EPROMs of EPROMs submitted (che the three sets of EPROMs this data. We shall assume t we produce differ from this d a contained in the EPROMs	submitted of he respons ata. Thus,	contain ibility fo the cus	the id	denti ors o	ical o	the mask	ROM data
	Ch	ecksum co	ode for entire EPROM area			(h	nexa	decir	nal notation	n)

## EPROM Type:

27C256	27C512			
Low-order 5-bit data 2FFF <sub>16</sub> 12.0K 2FFF <sub>16</sub> 4000 <sub>16</sub> 12.0K 6FFF <sub>16</sub> 7FFF <sub>16</sub>	Low-order 5-bit data 2FFF <sub>16</sub> 12.0K 2FFF <sub>16</sub> 4000 <sub>16</sub> 12.0K 6FFF <sub>16</sub> 12.0K			

Set "FF16" in the shaded area.

Set "1112" in the area of low-order and high-order 5-bit data.



Mask ROM number	Mask RO	er
-----------------	---------	----

## 4500 SERIES MASK ROM ORDER CONFIRMATION FORM SINGLE-CHIP MICROCOMPUTER M34524MC-XXXFP RENESAS TECHNOLOGY

	sume the responsibility for er mask file. Thus, extreme care	rors only if the mask ROM da e must be taken to verify the u ust be-3.5 inch 2HD type an	by the mask file generating utility. We shall asta on the products we produce differs from this mask file in the submitted floppy disk. d DOS/V format. And the number of the mask
	File code		(hexadecimal notation)
	Mask file name		.MSK (equal or less than eight characters)
<b>*2</b> .		k Specification Form (64P)	form for the type of package being ordered 6N for M34524MC-XXXFP) and attach to the
<b>*3.</b>	Usage conditions For our reference when of usage of the products you		e reply to the following questions about the
	(1)Which operation source  Ceramic resonator  RC oscillation  External clock input  Other( Ring oscillator  Quartz-crystal oscilla	What frequency f(XIN)=	do you use? MHz
	(2)What is the voltage of p	ower supply (VDD) you us Typ.=V	e? Max.=V
	(3)What is the ambient tem Min.= °C	perature you use? Typ.= °C	Max.= °C
	(4)Do you use the power d Not use Use only POF2 instru	Use only PC	tion and POF2 instruction)? OF instruction structions
	(5)Do you use the voltage Not use	-	
	(6)Do you use the A-D con Not use		
	(7)Do you use the serial I/0  Not use Use		
	Thank you cooperation.		

\*4. Comments

