



## PCI and PCIe Bridge Cross Reference

PCI Express Bridges				
Manufacturer	Part Number	IDT Part Number	Notes	
PLX	PEX8114-BC13BI	Tsi384-133IL	Note: Refer to conversion guide for differences. Tsi384 is compatible with earlier ** revisions.	
	PEX8114-**13BI	Tsi384-133IL		
	PEX8114-BC13BI G	Tsi384-133ILV	Note: Refer to conversion guide for differences. Tsi384 is compatible with earlier ** revisions.	
	PEX8114-**13BI G	Tsi384-133ILV		
	PEX8111-AA66BC	Tsi381-66IL	Note: Refer to conversion guide for differences.	
	PEX8111-BB66BC	Tsi381-66IL		
	PEX8111-AA66BC F	Tsi381-66ILV		
PEX8111-BB66BC F	Tsi381-66ILV			
	PEX8112-AA66BI F	Tsi381-66ILV		
PCI to PCI Bridges				
Manufacturer	Part Number	IDT Part Number		
Intel	EG21152BB SL7T7	Tsi352-66CQY	Please contact your IDT representative for other part numbers and compatible bridges	
	S21152BB	Tsi352-66CQ		
Pericom	PI7C8140AMAE	Tsi340-66CQY		
	PI7C8150MA	Tsi350A-66CQ		
	PI7C8150MA-33	Tsi350A-66CQ		
	PI7C8150BMA	Tsi350A-66CQ		
	PI7C8150BMA-33	Tsi350A-66CQ		
	PI7C8150AMA	Tsi350A-66CQ		
	PI7C8150AMA-33	Tsi350A-66CQ		
	PI7C8150BMAE	Tsi350A-66CQY		
	PI7C8150AMAE	Tsi350A-66CQY		
	PI7C8150AMAE-33	Tsi350A-66CQY		
	PI7C8150ANDE	Tsi350A-66CLV		
	PI7C8150BNDE	Tsi350A-66CLV		
	PI7C8152AMAE	Tsi352-66CQY		
PI7C8152AMA	Tsi352-66CQ			
PLX	PCI6140-AA33PC G	Tsi340-66CQY		
	PCI6150-BB66PC	Tsi350A-66CQ		
	PCI6150-BB66PC G	Tsi350A-66CQY		
	PCI6150-BB66BC G	Tsi350A-66CLV		
	PCI6152-CC33PC G	Tsi352-66CQY		
	PCI6152-CC33PC	Tsi352-66CQ		
TI	PCI2050BPPM	Tsi350A-66CQ		
	PCI2050BPDV	Tsi350A-66CQY		
	PCI2050BPDVG4	Tsi350A-66CQY		
	PCI2050PPM	Tsi350A-66CQ		Tsi350A compatible with earlier revision PCI2050 sockets
	PCI2050PDV	Tsi350A-66CQY		Note: Refer to conversion guide for differences.
	PCI2250PCMG4	Tsi352-66CQY		
	PCI2250PCM	Tsi352-66CQ		

### PCI Express Bridge Package Variants

Tsi384-133IL	256 ball BGA (17x17mm) Industrial
Tsi384-133ILV	256 ball BGA (17x17mm) Industrial, RoHS
Tsi381-66IL	144 ball BGA (13x13mm) Industrial
Tsi381-66ILV	144 ball BGA (13x13mm) Industrial, RoHS

### PCI-PCI Bridge Package Variants

Tsi340-66CQY	128 pin PQFP (23x17mm footprint) RoHS
Tsi350A-66CQ	208 pin PQFP (31x31mm footprint)
Tsi350A-66CQY	208 pin PQFP (31x31mm footprint) RoHS
Tsi350A-66CLV	256 ball BGA (17x17mm footprint) RoHS
Tsi352-66CQY	160 pin PQFP (32x32mm footprint) RoHS
Tsi352-66CQ	160 pin PQFP (32x32mm footprint)

**Note:** For further product documentation and for details on conversion to IDTPCI-PCI bridges, please refer to the conversion guides and design tool documentation