


I_{cc} vs V_{cc}

(High-speed on-chip oscillator mode)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C) — 85degreesC — 25degreesC
R5F21258SDFP(Topr=-40 to 85degrees C) — -40degreesC
divide-by-8
XIN clock off
High-speed on-chip oscillator on fOCO = 20 MHz
Low-speed on-chip oscillator on = 125 kHz



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.