


IOH vs VOH

(P0_0 to P0_3,P0_5,P1_0 to P1_7,P3_3 to P3_5,P4_5)

Prepared on Feb. 14, 2008

R8C/2K Group
Vcc=3V

— 85degreesC — 25degreesC
— -40degreesC



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.