



SYMBOLS	LIMITS		INCHES	
	MIN	MAX	MIN	MAX
A	.160	.185		
A1	.015	.035		
b	.015	.020		
b1	.050	.065		
C	.008	.012		
D	1.240	1.260		
E	.600	.620		
E1	.530	.550		
e	.090	.110		
eA	.610	.670		
L	.120	.150		
∠	0°	15°		
N	24			
Q1	.060	.080		
S	.060	.080		

JEDEC	EXCEPTIONS
STD-MO-015 (AA)	A1=.020-.070 b=.016-.020

TOLERANCES UNLESS OTHERWISE SPECIFIED  
FRAC DEC ANGLES  
± - ± - ± -



**Integrated Device Technology, Inc.**  
3236 Scott Blvd., Santa Clara, CA 95051  
(408) 727-6116 TWX: 910-338-2070

APPROVALS DATE  
DRAWN *AA* 7/88  
CHECKED  
*MF* 8/88

24 LD P-DIP MKT DWG  
(600 MIL)

SCALE	SIZE	DRAWING NO.	REV
N/A	A	PSC-4010	03
DO NOT SCALE DRAWING			SHEET 2 OF 2