



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	01/08/11	DP
01	PACKAGE HEIGHT UPDATED	03/18/11	DP
02	PACKAGE HEIGHT UPDATED	04/29/11	JG




TOP VIEW

A	MAX.	SLP
	NDM.	1.15
	MIN.	1.10



BOTTOM VIEW



SIDE VIEW

TOLERANCES UNLESS SPECIFIED
 DECIMAL ANGULAR
 XXX± ±
 XXXXX ±

APPROVALS DATE
 DRAWN DP 01/08/11
 CHECKED

SIZE C
 DRAWING No. PSC-4338

DO NOT SCALE DRAWING SHEET 1 OF 2

www.IDT.com FAX: (409) 284-9591


IDT 6024 Silver Creek Valley Road
 San Jose, CA 95138
 PHONE: (409) 284-8200

TITLE CN/CNG10 PACKAGE OUTLINE
 5.0x 3.2 mm BODY
 1.27 mm PITCH COL

REV 02


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	01/08/11	DP
01	PACKAGE HEIGHT UPDATED	03/18/11	DP
02	PACKAGE HEIGHT UPDATED	04/29/11	JG

PIN #1 IDENTIFICATION
CHAMFER 0.300 x 45°



CNG10 RECOMMENDED LAND PATTERN
(PCB TOP VIEW)

NOTES: ALL DIMENSIONS ARE IN MILLIMETERS.

TOLERANCES UNLESS SPECIFIED		 8024 Silver Creek Valley Road San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591 www.idt.com	
DECIMAL	ANGULAR	TITLE: CNG10 PACKAGE OUTLINE BODY: 5.0x 3.2 mm COL: 1.27 mm PITCH	
±	±	APPROVALS	DATE
XXXX	XXXX	DP	01/08/11
XXXX	XXXX	CHECKED	
SIZE	DRAWING No.	REV	
C	PSC-4338	02	
DO NOT SCALE DRAWING		SHEET 2 OF 2	