


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	1/16/13	RC
01	COMBINE POD & LAND PATTERN	7/15/13	KS



TOFP 44-PIN PACKAGE

All dimensions in Millimeters

SYMBOL	MIN	MAX
N		44
A	-	1.20
A1	0.05	0.15
A2	0.95	1.05
b	0.3	0.45
c	0.09	0.20
D		12.00 BASIC
D1		10.00 BASIC
D2		8.00 Ref
B		12.00 BASIC
E1		10.00 BASIC
B2		8.00 Ref
e		0.80 BASIC
L	0.45	0.75
q	0°	7°
GGC	-	0.08


TOLERANCES UNLESS SPECIFIED
 DECIMAL ±
 ANGULAR ±
 XXX
 XXXX
 XXXX

IDT 6024 Silver Creek Valley Road
 San Jose, CA 95138
 PHONE: (408) 294-8200
 WWW.IDT.COM FAX: (408) 284-8591

TITLE DE/DEG44 PACKAGE OUTLINE
 DRAWN 10.0 mm SQ BODY
 CHECKED 0.80 mm PITCH TOFP

APPROVALS DATE
 SIZE C DRAWING No. PSC-4453
 DO NOT SCALE DRAWING SHEET 1 OF 2


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	1/16/13	RC
01	COMBINE POD & LAND PATTERN	7/15/13	KS



RECOMMENDED LAND PATTERN DIMENSION

NOTES:

1. ALL DIMENSION ARE IN mm. ANGLES IN DEGREES.
2. TOP DOWN VIEW. AS VIEWED ON PCB.
3. LAND PATTERN IN BLUE. NSMD PATTERN ASSUMED.
4. LAND PATTERN RECOMMENDATION PER IPC-7351B LP CALCULATOR.

TOLERANCES UNLESS SPECIFIED		 8024 Silver Creek Valley Road San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8991 www.idt.com	
DECIMAL	±	ANGULAR	±
XXX±			
XXXX±			
APPROVALS	DATE	TITLE DE/DEG44 PACKAGE OUTLINE	
DRAWN <i>024C</i>	01/16/13	10.0 mm SQ BODY	
CHECKED		0.80 mm PITCH TOPP	
SIZE	DRAWING No.	REV	
C	PSC-4453	01	
DO NOT SCALE DRAWING			SHEET 2 OF 2