





REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	1/14/13	RC
01	COMBINE POD & LAND PATTERN	06/24/13	KS



DIMENSIONS (mm are the original dimensions)


UNIT	A	A1	A2	A3	b <sub>p</sub>	c	D	D(1)	D <sub>h</sub>	E(1)	E <sub>h</sub>	e	HD	HE	L	L <sub>p</sub>	v	w	y	Z <sub>D</sub> (1)	Z <sub>E</sub> (1)	theta
max.	1.2	0.15	1.05	0.25	0.27	0.20	14.1	7.1	14.1	7.1	14.1	0.5	16.15	16.15	1	0.75	0.2	0.08	0.08	1.15	1.15	7°
mm	1.2	0.05	0.95	0.17	0.09	0.09	13.9	6.1	13.9	6.1	13.9	0.5	15.85	15.85	1	0.45	0.2	0.08	0.08	0.85	0.85	0°

Note

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.


TOLERANCES UNLESS SPECIFIED		<b>6024 Silver Creek Valley Road</b> San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591 WWW.IDT.COM	
DECIMAL	ANGULAR	APPROVALS: DATE: TITLE: EVG100 PACKAGE OUTLINE DRAWN: 08/01/14/13 14.0 mm SQ BODY CHECKED: 08/01/14/13 1.0 mm THICK 0.5 mm PITCH QFP	
XXX	±	SIZE	DRAWING No. PSC-4422
XXXX		DO NOT SCALE DRAWING	REV 01
XXXX			SHEET 1 OF 2

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	1/14/13	RC
01	COMBINE POD & LAND PATTERN	06/24/13	KS



**RECOMMENDED FOOT PRINT DIMENSION**

- NOTES:**
1. ALL DIMENSION ARE IN mm. ANGLES IN DEGREES.
  2. TOP DOWN VIEW. AS VIEWED ON PCB.
  3. LAND PATTERN IN BLACK. NSMD PATTERN ASSUMED.
  4. LAND PATTERN RECOMMENDATION PER IPC-7351B LP CALCULATOR.

TOLERANCES UNLESS SPECIFIED		 <b>IDT</b> 6024 Silver Creek Valley Road San Jose, CA 95138 PHONE: (408) 284-8200 WWW.IDT.COM FAX: (408) 284-8591	
DECIMAL	ANGULAR		
XXX±	±		
XXXX±			
APPROVALS	DATE	TITLE	
DRAWN	06/24/13	EVC100 PACKAGE OUTLINE	
CHECKED		14.0 mm SQ BODY	
		1.0 mm THICK 0.5 mm PITCH QFP	
		SIZE	DRAWING No.
		C	PSC-4422
		DO NOT SCALE DRAWING	REV
			01
			SHEET 2 OF 2