




TOP VIEW



BOTTOM VIEW



SIDE VIEW



RECOMMENDED LAND PATTERN
(PCB Top View, NSMD Design)

| | MIN. | NOM. | MAX. |
|----|----------|-------|-------|
| D | 14.35 | 14.50 | 14.65 |
| E | 12.35 | 12.50 | 12.65 |
| D2 | 8.80 | 8.90 | 9.00 |
| E2 | 10.20 | 10.30 | 10.40 |
| b | 0.90 | 1.00 | 1.10 |
| L | 1.40 | 1.50 | 1.60 |
| e | 1.50 BSC | | |
| H | 2.55 | 2.80 | 3.05 |
| t | 0.70 | 0.80 | 0.90 |
| h | 1.85 | 2.00 | 2.15 |
| J | 1.05 Ref | | |
| K | 1.10 Ref | | |
| M | 1.60 | 1.75 | 1.90 |

NOTES:

1. JEDEC compatible.
2. All dimensions are in mm and angles are in degrees.
3. Use ± 0.05 mm for the non-toleranced dimensions.
4. Numbers in () are for references only.