






JEITA Package Code	RENESAS Code	Previous Code	MASS (Typ) [g]
SC-82AB	PTSP0004ZA-A	CMPAK-4(T) / CMPAK-4(T)V	0.006



Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
A	0.8	—	1.1
A <sub>1</sub>	0	—	0.1
A <sub>2</sub>	0.8	0.9	1.0
A <sub>3</sub>	—	0.25	—
b	0.25	0.3	0.4
b <sub>1</sub>	0.35	0.4	0.5
c	0.1	0.16	0.26
D	1.8	2.0	2.2
E	1.15	1.25	1.35
e	—	0.65	—
e <sub>2</sub>	—	0.6	—
H <sub>E</sub>	1.8	2.1	2.4
L	0.3	—	0.7
L <sub>1</sub>	0.1	—	0.5
L <sub>P</sub>	0.2	—	0.6
x	—	—	0.05
y	—	—	0.05
Q	—	0.2	—