



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	35.0	—
E	—	35.0	—
v	—	—	0.20
w	—	—	0.30
A	—	—	2.8
A_1	0.4	0.5	0.6
\oplus	—	1.0	—
b	0.5	0.6	0.7
x	—	—	0.1
y	—	—	0.2
Z_D	—	1.5	—
Z_E	—	1.5	—
D_1	19.7	19.8	19.9
E_1	19.7	19.8	19.9