


## 272-PIN PLASTIC BGA (CAVITY DOWN ADVANCED TYPE) (29x29)



ITEM	MILLIMETERS
A	29.00±0.20
D	29.00±0.20
E	1.80
F	1.27 (T.P.)
G	0.60±0.10
H	0.90
J	1.50±0.20
K	0.15
L	φ0.75±0.15
M	0.30
N	0.25 MIN.
P	0.10
Y	C1.5
Z	C0.5

S272S2-127-C6-3