

JEITA Package Code

RENESAS Code

Previous Code





MASS[Typ.]

P-QFP48-7x10-0.65

PRQP0048JA-A

48P6S-A

0.3g



Detail F

NOTE)

1. DIMENSIONS $*1$ AND $*2$ DO NOT INCLUDE MOLD FLASH.
2. DIMENSION $*3$ DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	9.8	10.0	10.2
E	6.8	7.0	7.2
A_2	—	1.85	—
H_D	11.7	12.0	12.3
H_E	8.7	9.0	9.3
A	—	—	2.15
A_1	0	0.1	0.2
b_p	0.2	0.25	0.35
c	0.13	0.15	0.2
θ	0°	—	10°
Ⓢ	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z_D	—	0.775	—
Z_E	—	0.575	—
L	0.3	0.5	0.7