






JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-QFP56-10x10-0.65	PRQP0056JB-C	FP-56CV	0.51g



NOTE)
 1. DIMENSIONS *1 AND *2*
 DO NOT INCLUDE MOLD FLASH
 2. DIMENSION *3 DOES NOT
 INCLUDE TRIM OFFSET.



Terminal cross section
 (Ni/Pd/Au plating)



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	10.0	—
E	—	10.0	—
A ₂	—	2.20	—
H _D	12.5	12.8	13.1
H _E	12.5	12.8	13.1
A	—	—	2.54
A ₁	0.01	0.1	0.2
b _p	0.22	0.27	0.32
b ₁	—	—	—
c	0.10	0.15	0.20
c ₁	—	—	—
θ	0°	—	8°
e	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z _D	—	0.775	—
Z _E	—	0.775	—
L	0.45	0.60	0.75
L ₁	—	1.40	—