




| | | | |
|----------------------|--------------|---------------|------------|
| JEITA Package Code | RENESAS Code | Previous Code | MASS[Typ.] |
| P-SDIP20-6.3x19-1.78 | PRDP0020BA-A | 20P4B | 1.0g |



SEATING PLANE

- NOTE)
1. DIMENSIONS **1* AND **2* DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION **3* DOES NOT INCLUDE TRIM OFFSET.

| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|-------|-------|
| | Min | Nom | Max |
| e ₁ | 7.32 | 7.62 | 7.92 |
| D | 18.8 | 19.0 | 19.2 |
| E | 6.15 | 6.3 | 6.45 |
| A | — | — | 4.5 |
| A ₁ | 0.51 | — | — |
| A ₂ | — | 3.3 | — |
| b _p | 0.38 | 0.48 | 0.58 |
| b ₃ | 0.9 | 1.0 | 1.3 |
| c | 0.22 | 0.27 | 0.34 |
| θ | 0° | — | 15° |
| e | 1.528 | 1.778 | 2.028 |
| L | 3.0 | — | — |