



JEITA Package code	RENESAS code	Previous code	MASS(TYP.)[g]
P-SOP28-7.5x18-1.27	PRSP0028DL-A	T28MR-127-PAA	0.77



Terminal cross section



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	17.80	18.00	18.20
E	7.30	7.50	7.70
A ₂	2.25	2.30	2.35
A ₁	0.10	—	0.30
A	—	—	2.65
A ₃	—	0.25	—
bp	0.39	—	0.48
b ₁	0.38	0.41	0.43
c	0.25	—	0.31
c ₁	0.24	0.25	0.26
θ	0°	—	8°
H _E	10.10	10.30	10.50
L _p	0.70	—	1.00
e	—	1.27	—
L ₁	—	1.40	—