


54-PIN PLASTIC TSOP (II) (10.16 mm (400))



NOTES

- Each lead centerline is located within 0.13 mm of its true position (T.P.) at maximum material condition.
- "A" excludes mold flash. (Includes mold flash : 22.42 mm MAX.)

ITEM	MILLIMETERS
A	22.17±0.05
B	0.885 MAX.
C	0.80 (T.P.)
D	0.32 ^{+0.08} _{-0.07}
G	1.00
H	11.76±0.20
I	10.11±0.08
J	0.825±0.2
K	0.145 ^{+0.025} _{-0.015}
L	0.50
M	0.13
N	0.10
Q	0.10±0.05
R	3° ^{+5°} _{-3°}
S	1.1±0.1
T	0.25
U	0.6±0.15

S54G5-80-9NF-1