







TOP VIEW



BOTTOM VIEW




SIDE VIEW



DETAIL A

Table 1: Dimensions of wettable flank (DETAIL A)

Symbol	Unit (mm)	
	MIN	MAX
FD	0.100	-
FW	0.001	0.075



RECOMMENDED LAND PATTERN
(PCB Top View, NSMD Design)

NOTES:

- JEDEC compatible.
- All dimensions are in mm and angles are in degrees.
- Use ± 0.05 mm for the non-toleranced dimensions.
- Numbers in () are for references only.
- Wettable flank (step cut).