

Option List HD6432142,HD6432132,HD6432130

Please check off the appropriate applications by , or within and enter the necessary information.

(1) ROM size

<input type="checkbox"/>	HD6432142	:	64-kbytes
<input type="checkbox"/>	HD6432132	:	64-kbytes
<input type="checkbox"/>	HD6432130	:	32-kbytes

(2) System Oscillator(OSC1,OSC2)

<input type="checkbox"/>	Crystal oscillator	f =		MHz
<input type="checkbox"/>	External clock	f =		MHz

Date of order	
Customer	
Department	
Name	
ROM code Name	
LSI number (Renesas entry)	

(3) Power Supply Voltage/Maximum Operating Frequency

<input type="checkbox"/>	V _{cc} = 4.5V to 5.5V (20 MHz max.)
<input type="checkbox"/>	V _{cc} = 4.0V to 5.5V (16 MHz max, Only Single-Chip Mode is available in JE specification.)
<input type="checkbox"/>	V _{cc} = 2.7V to 5.5V (10 MHz max.)
<input type="checkbox"/>	V _{cc} = 4.0V to 5.5V (10 MHz max, Low EMI Noise version, Only Single-Chip Mode is available.)

Notes 1.Please select the power supply voltage/operating frequency version according to the power supply voltage used.

Example: For use at V_{cc} = 4.5V to 5.5V/f = 10MHz
select V_{cc} = 4.5V to 5.5V(20MHz max.).

2.The power supply voltage and maximum operating frequency of the selected version should also be entered on the Single-Chip Microcomputer Ordering Specifications sheet.