

JEITA Package Code

RENESAS Code

Previous Code



MASS[Typ.]

P-LFQFP80-10x10-0.40


PLQP0080LA-A

80P6R-A


0.3g



Terminal cross section



Detail F



NOTE)

1. DIMENSIONS *1" AND *2" DO NOT INCLUDE MOLD FLASH.
2. DIMENSION *3" DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	9.9	10.0	10.1
E	9.9	10.0	10.1
A_2	—	1.4	—
H_D	11.8	12.0	12.2
H_E	11.8	12.0	12.2
A	—	—	1.7
A_1	0	0.1	0.2
b_p	0.13	0.18	0.23
b_1	—	0.16	—
c	0.09	0.145	0.20
c_1	—	0.125	—
θ	0°	—	8°
@	—	0.4	—
x	—	—	0.07
y	—	—	0.10
Z_D	—	1.2	—
Z_E	—	1.2	—
L	0.35	0.5	0.65
L_1	—	1.0	—