





JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-LSSOP24-5.6x7.8-0.65	PLSP0024JB-A	24P2F-A	0.1g



Detail F

- NOTE)
1. DIMENSIONS *1" AND *2" DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION *3" DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	7.7	7.8	7.9
E	5.5	5.6	5.7
A ₂	—	1.15	—
H _D	—	—	—
H _E	7.4	7.6	7.8
A	—	—	1.45
A ₁	0	0.1	0.2
b _p	0.17	0.22	0.32
c	0.13	0.15	0.2
θ	0°	—	10°
ⓔ	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z _D	—	0.325	—
Z _E	—	—	—
L	0.3	0.5	0.7