


Terminal cross section  
(Ni/Pd/Au plating)



Detail F

NOTE)

1. DIMENSIONS<sup>\*\*1</sup> (Nom)<sup>\*\*AND\*\*2</sup> DO NOT INCLUDE MOLD FLASH.
2. DIMENSION<sup>\*\*3</sup> DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	10.06	10.5
E	—	5.50	—
A <sub>2</sub>	—	—	—
A <sub>1</sub>	0.00	0.10	0.20
A	—	—	2.20
b <sub>p</sub>	0.34	0.40	0.46
b <sub>1</sub>	—	—	—
c	0.15	0.20	0.25
c <sub>1</sub>	—	—	—
θ	0°	—	8°
H <sub>E</sub>	7.50	7.80	8.00
$\text{[e]}$	—	1.27	—
x	—	—	0.12
y	—	—	0.15
Z	—	—	1.42
L	0.50	0.70	0.90
L <sub>1</sub>	—	1.15	—