




JEITA Package Code
P-HXQFN40-5x5-0.40

RENESAS Code
PXQN0040LA-A

Previous Code
—

MASS[Typ.]
0.037g



(Ni/Pd/Au plating)

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	4.90	5.00	5.10
E	4.90	5.00	5.10
A ₂	—	—	—
A	—	—	0.50
A ₁	0	—	0.05
b	0.15	0.20	0.25
b ₁	—	—	—
e	—	0.40	—
L _p	0.35	0.40	0.45
x	—	—	0.10
y	—	—	0.08
y ₁	—	—	0.10
t	—	—	0.15
H _D	—	—	—
H _E	—	—	—
Z _D	—	—	—
Z _E	—	—	—
c	—	0.125	—
c ₁	—	—	—