

Selecting the Right Battery Chemistry for Automotive Safety Applications

Introduction

The automotive industry is quickly moving toward more electrification. The deployment of start-stop systems, emergency call (eCall) telematics, and hybrid vehicles is fueling the need for advanced battery management systems that not only charge the battery in a safe manner but also prolong its useful life. There are many battery chemistries available in the market today, which makes the selection decision more difficult when trying to pick the right one for a particular application, along with a suitable charging solution.

This white paper explains Lithium-ion (Li-ion) and Lithium iron phosphate (LFP or LiFePO_4) chemistries, including their characteristics and charging profiles. It also identifies charging solutions that derive the maximum energy from the battery while maximizing battery life and reliability.

Lithium-ion

The Li-ion battery is a rechargeable battery where lithium ions move from the negative electrode to the positive electrode during discharge and back when charging. They utilize an intercalated lithium compound as electrode material. The electrolyte, which allows for ionic movement, and the two electrodes are the fundamental components of a Li-ion battery cell. Generally, Li-ion batteries have high energy, but low power.

Figure 1 shows the charging profile of a Li-ion battery. It has a nominal voltage of 3.6V with an upper charge cutoff voltage of 4.1V and a lower charge cutoff voltage of 2.2V. Li-ion cells must be charged precisely according to the vendor recommendations to ensure reliability and safety. There are typically restrictions on charging the cell outside of the specified levels and outside of a recommended temperature range.




Figure 1. Li-ion charging profile

Between the lower and upper voltage levels, the charge current is typically recommended to be held constant and should be limited to the vendor recommended level to prevent battery damage.

Below the lower charge cutoff voltage, the battery should be charged with a very low current, typically 10% or less of the current used between the lower and upper voltage levels. This is often referred to as pre-charging the battery and is recommended for deeply depleted batteries. Some materials within the battery may degrade if it endures a prolonged state of deep discharge. Pre-charging is recommended to allow these materials to recover. Pre-charging is also a precaution that will prevent overheating in case the battery experienced an internal short circuit that led to the low cell voltage.

Charging the battery above the maximum charging voltage is also detrimental to the battery life. Short periods of overcharging can degrade the materials within the battery and lead to reduced energy capacity and a shorter lifetime. Extended periods of overcharging will cause metallic lithium to be plated on the anode while the cathode releases CO₂. This process can ultimately result in battery failure and a catastrophic combustion event.

Additionally, to maximize battery life, battery manufacturers often stipulate that the charging be performed within a limited temperature range. Charging most Li-ion battery technologies below freezing can cause metallic lithium to be plated on the anode. This is detrimental to battery life, as the plated lithium cannot be removed. Exposing the battery to elevated temperatures when charging also reduces battery life. According to the study “BU-410: Charging at High and Low Temperatures” published on batteryuniversity.com, cycling a Li-ion battery between 0% and 100% of full charge only a few times at elevated temperature can drastically reduce its capacity. In some cases, battery capacity can be reduced by more than 90%.

A simple way to achieve the vendor’s recommended charging profile is to use a dedicated charger, such as the ISL78692 Li-ion/Li-Polymer battery charger, which can perform the quickest charge in the safest manner. The ISL78692 allows a programmable constant charging current and comes pre-programmed with upper and lower charge cut-off levels that are ideal for most traditional Li-ion batteries. It also includes a cell temperature monitor to ensure that the battery is only charged within a temperature range that is programmable with an NTC thermistor.

Lithium Iron Phosphate

The LFP battery is a type of rechargeable battery that utilizes a nanoscale LiFePO₄ material as a cathode. LFP batteries have lower energy density than other Lithium batteries designed for use in consumer electronics; however, they have longer lifetimes, better power density and are inherently safer. The nano phosphate technology used in the cathode helps increase the cathode’s surface area exposed to the electrolyte. This allows faster lithium insertion resulting in more power and a higher current rating. This feature makes LFP a popular choice for replacing automotive starter batteries, where high peak power is needed.

LFP battery materials and the associated chemical reactions are also inherently more stable than other Li-ion chemistries, so it is not often that LFP batteries are damaged if mishandled or misused. The chemical bonds within the battery materials are stronger, making them more stable and resistant to extreme conditions. They are also less likely to release gasses when overcharged and therefore less likely to experience the phenomenon called “vent with flame.” Their inherent robustness makes them an attractive option for small backup batteries in applications where safety concerns are front and center. Many vehicle component makers cite this as a principal reason that LFP cells are frequently chosen for automotive applications.

Figure 2 shows the recommended charging profile of an LFP battery. It is very similar to that of a Li-ion cell; however, notice that the safe charging range is at different cell voltages. It has a nominal float voltage of

3.2V with an upper charge cutoff voltage of 3.65V and a lower charge cutoff voltage of 2.5V. As with Li-ion batteries, charging an LFP outside of the vendor defined upper and lower charge thresholds can still be detrimental to battery life, although to a much less extent. Between these levels, the charge current should be held constant within the range recommended for the particular cell. In this case, the vendor has recommended a current between 400mA and 500mA for maximum battery life. And similar to Li-ion batteries, charging should be performed within the stipulated temperature range.




Figure 2. Lithium iron phosphate charging profile

Since consumer electronics have typically favored Li-ion over LFP batteries for their higher energy density, there have traditionally been fewer dedicated charging solutions for LFP cells. However, given the recent adoption of LFP in automotive applications, new LFP chargers are being introduced. They provide an easy way to achieve the recommended charging profile for LFP batteries. For example, the Intersil ISL78693 single-cell LiFePO₄ battery charger for automotive eCall systems can be configured to provide the charging profile shown in Figure 2, and has built in features to ensure the battery is charged in a safe manner.

Similar to the ISL78692, the ISL78693 charging device offers a programmable charge current and comes preconfigured with lower and upper charge cutoff voltages that are intended for use with LFP batteries. It also includes an input that when paired with an NTC thermistor, allows the battery to be charged within a limited temperature window. Both the ISL78692 and ISL78693 are pin-to-pin compatible, allowing the quick migration, with no board redesign, of a Li-ion charging solution to the LFP battery chemistry.

Conclusion

The ongoing electrification of automobiles provides designers with an entirely new set of selection criteria, starting with the battery chemistry's end application. While the charging profile of a LFP battery is very similar to that of a Li-ion cell, the safe charging range is at different cell voltages. Because of the inherent robustness of LFP batteries, they are an attractive option for small backup battery eCall applications where safety concerns are front and center. Many vehicle component makers cite this as a principal reason that LFP cells are frequently chosen for this application. Automakers worldwide are installing eCall in their Vehicle to Infrastructure (V2I) systems. In the event of a crash, the eCall system automatically broadcasts its location via GPS and contacts the nearest 24-hour emergency call center for help.

Next Steps

- [Learn more about the ISL78693/92](#)
- [Download the datasheets](#)

About Renesas Electronics Corporation

Renesas Electronics Corporation delivers trusted embedded design innovation with complete semiconductor solutions that enable billions of connected, intelligent devices to enhance the way people work and live—securely and safely. A global leader in microcontrollers, analog, power, and SoC products, Renesas provides the expertise, quality, and comprehensive solutions for a broad range of Automotive, Industrial, Home Electronics, Office Automation and Information Communication Technology applications to help shape a limitless future. Learn more at [renesas.com](https://www.renesas.com)

+1 408-432-8888 | © Renesas Electronics America. All rights reserved. Renesas & Intersil (and design) are trademarks owned by Renesas Electronics Corporation or one of its subsidiaries. All other trademarks mentioned are the property of their respective owners.