

JEITA Package Code

RENASAS Code

Previous Code





MASS[Typ.]

P-HWQFN40-6x6-0.50

PWQN0040KB-A

40PJS-A

0.07g



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	5.9	6.0	6.1
E	5.9	6.0	6.1
A_2	—	0.75	—
A	—	—	0.8
A_1	0	0	0.05
b_p	0.15	0.2	0.25
e	—	0.5	—
L_p	0.2	0.3	0.4
x	—	—	0.05
y	—	—	0.05
Z_D	—	0.75	—
Z_E	—	0.75	—
D_2	—	4.73	—
E_1	—	4.73	—