


Package Outline Drawing

C69.5x5

69 LEAD HIGH DENSITY ARRAY PACKAGE



Rev 2, 2/12



SYMBOL	MILLIMETER			INCH		
	MIN	NOM.	MAX	MIN	NOM.	MAX
A	-	-	0.85	-	-	0.033
A3	0.020	0.050	0.080	0.001	0.002	0.003
A2	0.640	0.675	0.710	0.025	0.027	0.028
A1	0.120	0.130	0.140	0.005	0.005	0.006
b	0.150	0.200	0.250	0.006	0.008	0.010
D	5.00 BSC			0.197 BSC		
D2	2.780	2.880	2.980	0.109	0.113	0.117
E	5.00 BSC			0.197 BSC		
E2	1.940	2.040	2.140	0.076	0.080	0.084
eT	0.400			0.016		
eR	0.400			0.016		
K	0.200	0.250	0.300	0.008	0.010	0.012
L1	0.160	0.210	0.260	0.006	0.008	0.010
L2	0.230	0.280	0.330	0.009	0.011	0.013

TOLERANCES OF FORM AND POSITION

aaa	0.150	0.006
bbb	0.100	0.004
ddd	0.050	0.002
ccc	0.100	0.004
eee	0.100	0.004
fff	0.100	0.004



DETAIL "B" (3:1)(69X)