




JEITA Package Code	RENESAS Code	Previous Code	MASS (TYP.) [g]
P-TFQFP120-14x14-0.40	PTQP0120LB-A	P120GC-40-YEB-2	0.53



ITEM	MILLIMETERS
A	16.00±0.20
B	14.00±0.20
C	14.00±0.20
D	16.00±0.20
F	1.20
G	1.20
H	0.18±0.05
I	0.07
J	0.40 (T.P.)
K	1.00±0.20
L	0.50
M	0.17 <sup>+0.03</sup> <sub>-0.07</sub>
N	0.08
P	1.00±0.05
Q	0.10±0.05
R	3° <sup>+4°</sup> <sub>-3°</sub>
S	1.20MAX.
T	0.25
U	0.60±0.15

**NOTE**

Each lead centerline is located within 0.07 mm of its true position (T.P.) at maximum material condition.