

JEITA Package Code

RENESAS Code

Previous Code






MASS[Typ.]

P-HTFQFP100-14x14-0.50

PTQP0100KE-A

100PFW-A

0.5g



Detail F

NOTE)

1. DIMENSIONS $*1$ " AND $*2$ " DO NOT INCLUDE MOLD FLASH.
2. DIMENSION $*3$ " DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	13.9	14.0	14.1
E	13.9	14.0	14.1
A_2	—	1.0	—
H_D	15.8	16.0	16.2
H_E	15.8	16.0	16.2
A	—	—	1.2
A_1	0.05	0.1	0.15
b_p	0.17	0.22	0.27
c	0.09	0.145	0.20
θ	0°	—	8°
Ⓜ	—	0.5	—
x	—	—	0.08
y	—	—	0.08
Z_D	—	1.0	—
Z_E	—	1.0	—
L	0.4	0.5	0.6
D_2	—	7.3	—
E_1	—	6.3	—