

JEITA Package Code

RENESAS Code

Previous Code


MASS[Typ.]

P-LFBGA261-13x13-0.65

PLBG0261JA-A

261FHE

0.4g



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	13.0	—
E	—	13.0	—
v	—	—	0.15
w	—	—	0.20
A	—	—	1.4
A ₁	0.28	0.33	0.38
ϕ	—	0.65	—
b	0.35	0.4	0.45
x	—	—	0.08
y	—	—	0.10
Z _D	—	0.975	—
Z _E	—	0.975	—