

RA6T1 CPU Card BOM LIST

Product Name: RA6T1 CPU Card

Board Name : RA6T1 CPU Card (RTK0EMA170C00000BJ)

Schematic No : R12TU0091

Date : 2020/5/8

No.	Reference	Description	Manufacturer	PartNumber	Qty
1	CNA,CNB	CONN HEADR FEMALE 20POS .1 DL AU	Sullins Connector Solutions	SFH11-PBPC-D10-ST-BK	2
2	CN4	CONN RCPT USB2.0 MINI B SMD R/A	Hirose	UX60SC-MB-5ST	1
3	JP5	4Px2	Sullins Connector Solutions	NRPN042PAEN-RC	1
4	JP1,JP2,JP3,JP6	JP_3pin	Sullins Connector Solutions	NRPN031PAEN-RC	4
5	CN5,CN7	CONN HEADER XH TOP 5POS 2.5MM	JST	B5B-XH-A(LF)(SN)	2
6	CN10	CONN HEADER XH TOP 4POS 2.5MM	JST	B4B-XH-A(LF)(SN)	1

R12TU0092EJ0100



© 2020 Renesas Electronics Corporation. All rights reserved.

RA6T1 CPU Card BOM LIST

No.	Reference	Description	Manufacturer	PartNumber	Qty
7	JP4	JP_2pin	Sullins Connector Solutions	NRPN021PAEN-RC	2
8	C19	Capacitor (C3216)	Taiyo	LMK316BJ475KD-T C3216X7R1E475K160AC GRM319R61H475KA12D	1
9	C1,C4,C6,C7,C8,C9, C10,C11,C12,C13,C14 C15 C16 C17 C18	Capacitor (C1005)	Taiyo	EMK105B7104KV-F	21
10	C2,C3	Capacitor (C1005)	Taiyo	UMK105CH100DVHF	2
11	C21,C22,C23,C24,C25, C26,C27,C28,C29, C30,C31,C32,C33,C34 C35 C36 C37 C38	Capacitor (C1005)	Murata	GCM155R71H471KA37D	18
12	C43,C44,C45,C46,C47, C48,C51,C54	Capacitor (C1005)	Taiyo	UMK105BJ102KVHF	8
13	C5	Capacitor (C1005)	Taiyo	EMK105ABJ474MV-F	1
14	C49	Capacitor (C1005)	Taiyo	EMK316BJ106KD-T	1
15	R1,R6,R8,R14,R15,R16, R17,R18,R19,R20	Resistor (R1005)	Taiyo	RK73B1ETTP472J	26
16	R9,R11,R95	Resistor (R1005)	KOA	RK73B1ETTP473J	3

R12TU0092EJ0100



© 2020 Renesas Electronics Corporation. All rights reserved.

RA6T1 CPU Card BOM LIST

No.	Reference	Description	Manufacturer	PartNumber	Qty
17	R5,R24,R27,R29,R30 ,R32,R35,R38,R40,R 42,R44,R45,R56,R58 ,R59,R61,R64,R65,R 66,R67,R77,R78,R79 ,R86,R87,R88,R89,R 91	Resistor (R1005)	KOA	RK73H1ETTP1001F	28
18	R7,R10	Resistor (R1005)	KOA	RK73B1ETTP151J	2
19	R2,R13,R26,R28,R34 ,R36,R37,R39,R41,R 43,R92,R94	Resistor (R1005)	Panasonic	ERJ-2GE0R00X	12
20	R4	Resistor (R1005)	KOA	RK73B1ETTP103J	1
21	R74,R75,R76,R83,R8 4,R85	Resistor (R1005)	KOA	RK73B1ETTP202J	6
22	R3,R93	Resistor (R1005)	KOA	RK73B1ETTP220J	2
23	R23,R31,R33,R57,R6 2,R63	Resistor (R1005)	KOA	RK73H1ETTP1502F	6

R12TU0092EJ0100



© 2020 Renesas Electronics Corporation. All rights reserved.

RA6T1 CPU Card BOM LIST

No.	Reference	Description	Manufacturer	PartNumber	Qty
24	R12,R46,R47,R48,R49,R68,R69,R70	Resistor (R1005)	KOA	RK73H1ETTP2402F	8
25	SW1	Switch	Panasonic	EVQ-5PN04K	1
26	U2	MCU	Renesas	R7FS124773A01CFM#AA1	1
27	U3	Zener diode	Semtech Corporation	RClamp0582N	1
28	U1	MCU	Renesas	R7FA6T1AD3CFP	1
29	U4,U5,U6,U7	Open drain buffer	TI	SN74LVC07APW	4
30	U8	LDO	Renesas	ISL9005AIRNZ-T	1
31	X1	Xtal 10MHz	Abracon	ABLS-10.000MHz-B4-T	1
32	LED1,LED2,LED3	LED	Würth Elektronik	150060VS75000	3

R12TU0092EJ0100



© 2020 Renesas Electronics Corporation. All rights reserved.

RA6T1 CPU Card BOM LIST

No.	Reference	Description	Manufacturer	PartNumber	Qty
33	D1	Diode	NEXPERIA	PMEG2005EH, 115	1

Unmounted

34	CN1	6P	-	-	-
35	CN2	10Px2	-	-	-
36	CNC	CONN HEADR FEMALE 26POS .1 DL AU	-	-	-
37	CN9	6Px2 2.54mm pitch	-	-	-
38	CN6	4P 2.54mm pitch	-	-	-
39	CN8	6P 2.54mm pitch	-	-	-
40	CN3	3Px2	-	-	-
41	C50,C52,C53	Capacitor (C1005)	-	-	-
42	R25	Resistor (R1005)	-	-	-
43	TP1,TP2,TP3,TP4,TP5,	Test pin	-	-	-

R12TU0092EJ0100



© 2020 Renesas Electronics Corporation. All rights reserved.