



Integrated Device Technology

Tsi578™ Serial RapidIO® Switch

POWER MANAGEMENT | ANALOG & RF | INTERFACE & CONNECTIVITY | CLOCKS & TIMING | MEMORY & LOGIC | TOUCH & USER INTERFACE | VIDEO & DISPLAY | AUDIO

FEATURES

Serial RapidIO Interfaces


- 80 Gbits/s aggregate bandwidth
- Low latency with cut-through capability
- Enhanced SerDes for low power solution
- *RapidIO Interconnect Specification (Revision 1.3)* compliant
- High performance hardware multicast

Tsi578 enhances system scalability and performance through support for mixed port configurations and extensive fabric management features.

- Error management extensions
 - Proactive issue notification
- Port flexibility fulfills multiple I/O bandwidth requirements:
 - Up to eight 4x mode ports or sixteen 1x mode ports
 - Port frequency configuration to 1.25, 2.5, and 3.125 Gbits/s
 - Support for mixed speed and width configurations
- Integrated high-speed, full-duplex SerDes with 8b/10b encoding
 - Receiver equalization, transmit pre-emphasis, transmit voltage swing
 - IEEE 1149.6 support
 - Lane swap to ease signal layout routing
- Enhanced non-blocking internal switching fabric
 - Traffic management through scheduling algorithms
 - Performance monitoring on individual ports
 - Programmable buffer depth
 - Provisions to eliminate low priority packet starvation
- Supports packet routing tables for 64,000 endpoints

Other Device Capabilities

- I²C Interface:
 - Master and Slave
 - Configuration through register initialization
- Hot Swappable ports
 - Enables use in field replaceable blade applications



Device Overview

The Tsi578 is a third generation RapidIO switch supporting 80 Gbits/s aggregate bandwidth. The Tsi578 is part of a family of switches that enable customers to develop systems with robust features and high performance at low cost.

The Tsi578 provides designers and architects with maximum scalability to design the device into a wide range of applications. Flexible port configurations can be selected through multiple port width and frequency options.

Building on the industry leading Tsi568ATM Serial RapidIO Switch, the Tsi578 contains all the benefits of its predecessor plus enhances the fabric switching capabilities through the addition of multicast, traffic management through scheduling algorithms, programmable buffer depth, and fabric performance monitoring to supervise and manage traffic flow.

Embedded applications further benefit from the ability to route packets to over 64,000 endpoints through hierarchical lookup tables, independent unicast and multicast routing mechanisms, and error management extensions that provide proactive issue notification to the fabric controller. In addition, the Tsi578 supports both in-band serial RapidIO access and out-of-band access to the full fabric register set through the I²C interface.

BENEFITS

- Scalability: Single solution for mesh, fabric, and aggregated systems
- Performance: Improved system and distributed processing performance
- Power: SerDes implementation for low power solution

Specifications

- Technology: 0.13um
- Voltage: 1.2V and 3.3V
- Low power consumption
- Package: 675 ball, 27mm x 27mm, 1mm ball pitch FCBGA
- Rated for commercial and industrial temperatures
- Forward compatible with the Tsi568A Serial RapidIO Switch allowing easy migration for existing systems.

Target Markets


- Wireless Infrastructure
 - Node B, Radio Network Controller, Media Gateway
- Communications Wireline Infrastructure
 - Multiservice WAN Switches, 1 to 10 Gbit Ethernet Switches, 1 to >10 Gbit Routers, DSLAMs
- Storage
 - Storage Area Networks, Network Attached Storage, High-Performance Work Stations, Multi-service Access Nodes, Carrier-grade VoIP
- Video Infrastructure
 - Broadcast, imaging, and encoding
 - Architecture Standards
 - ATCA, MicroTCA, VXS, VPX

Discover what IDT know-how can do for you: www.IDT.com

Typical Applications

The Tsi578 can be used in many embedded communication applications. It provides chip-to-chip interconnect between I/O devices and can replace existing proprietary backplane fabrics for board-to-board interconnect which improves system cost and product time-to-market.

Processor Farm Mezzanine



The Tsi578 provides traffic aggregation through packet prioritization when it is used with RapidIO-enabled I/O devices. When it is in a system with multiple RapidIO-enabled processors it provides high performance peer-to-peer communication through its non-blocking switch fabric.

Switch Carrier Blade

