

Accessories information for R8C, M32R, M16C, 740, and 720 Families

(Excepting for related information for E1, E20 and E100)

- [Converter for IC Packages : Exclusively for M32R Family](#)
- [Converter for IC Packages : Exclusively for R8C Family](#)
- [Converter for IC Packages : Exclusively for M16C/Tiny Series](#)
- [Converter for IC Packages : Exclusively for M16C Family](#)
- [Converter for IC Packages : Exclusively for H8/300H Tiny Series](#)
- [Converter for IC Packages : Exclusively for 740 Family 740 Series 75xx Group](#)
- [Converter for IC Packages : Exclusively for 740 Family](#)
- [Converter for IC Packages : Exclusively for 4500 Series](#)
- [General-purpose Product \(Pitch Converter Board\)](#)
- [General-purpose Product \(for Height Adjustment\)](#)
- [General-purpose Product \(for Direction Converting\)](#)
- [General-purpose Product \(Dummy ICs and Related\)](#)
- [Standard Pitch \(2.54mm\) Converter](#)
- [Protection Board](#)
- [Temporary Target Board](#)
- [Oscillator Board](#)
- [Optional Cable](#)
- [LCC Socket](#)

Note: Visit the website (<http://www.renesas.com/>) for the latest status of products.

Converter for IC Packages : Exclusively for M32R Family

- M32170T-PTC [Discontinued] Converter for In-circuit Connection (for 32170, 32174 Group)
- M32171T-PTC [Discontinued] Converter for In-circuit Connection (for 32171 Group)
- M32173T-PTC [Discontinued] Converter for In-circuit Connection (for 32172, 32173 Group)
- M32176T-PTC Converter Board for In-circuit Connection (for 32176 Group)
- M32182T2-PTC [Discontinued] Converter for In-circuit Connection (for M32182 Group)
- M32186T2-PTC Converter for In-circuit Connection (for M32185, M32186 Group)
- M32192T2-PTC Converter for In-circuit Connection (for M32192 Group)

Converter for IC Packages : Exclusively for R8C Family

- R0E521134CFG00 Converter Board for 32-pin 0.8-mm-pitch LQFP (for R8C/10, R8C/11, R8C/12, R8C/13 Group)
- R0E521174CSJ00 Converter Board for 20-pin 0.65-mm-pitch LSSOP
(for R8C/14, R8C/15, R8C/16, R8C/17, R8C/18, R8C/19, R8C/1A, R8C/1B, R8C/28, R8C/29 Group)
- R0E521174CDB00 Converter Board for 20-pin 1.778-mm-pitch SDIP (for R8C/18, R8C/19, R8C/1A, R8C/1B Group)
- R0E521237CFK00 Converter Board for 48-pin 0.5-mm-pitch LQFP (for R8C/20, R8C/21, R8C/22, R8C/23 Group)
- R0E521258CFJ00 Converter Board for 52-pin 0.65-mm-pitch LQFP (for R8C/24, R8C/25 Group)
- R0E521276CFG00 Converter Board for 32-pin 0.8mm pitch LQFP (for R8C/26, R8C/27 Group)
- R0E5212L4CFG00 Converter Board for 32-pin 0.8mm pitch LQFP (for R8C/2K, /2L Group)

Converter for IC Packages : Exclusively for M16C/Tiny Series

- M30260T-48FPD Converter Board for 48-pin 0.5-mm-pitch LQFP (for M16C/26A Group)
- M30263T-42SSB [Discontinued] Converter Board for 42-pin 0.8-mm-pitch SSOP (for M16C/26A Group)
- M30290T-80FPD Converter Board for 80-pin 0.5-mm-pitch LQFP (for M16C/28 Group, M16C/29 Group)
- M30291T-64FPD Converter Board for 64-pin 0.5-mm-pitch LQFP (for M16C/28 Group, M16C/29 Group)
- M30280T-85LGF [Discontinued] Converter Board for 85-pin 0.65mm pitch TFLGA (for M16C/28 Group)

Converter for IC Packages : Exclusively for M16C Family

- M30100T-PTC Converter for 32-pin 0.8mm-pitch QFP for M30100T-PRB (for M16C/10 Group M30100)
- M30102T-PTC Converter for 48-pin 0.5mm-pitch QFP for M30100T-PRB (for M16C/10 Group M30102)
- M30201T-52SP [Discontinued]
Converter for Connecting Pod Probe M30201T-PRB to 52-pin 1.778mm-pitch SDIP (for M30201 Group)
- M30201T-56FP [Discontinued]
Converter for Connecting Pod Probe M30201T-PRB to 56-pin 0.65mm-pitch QFP (for M30201 Group)
- M30260T-48FPD Converter Board for 48-pin 0.5-mm-pitch LQFP (for M16C/Tiny Series)
- M30262T-PTC Converter Board for 48 pin 0.5mm pitch QFP (for M16C/26 Group M30262)
- M30263T-42SSB Converter Board for 42-pin 0.8mm-pitch SSOP (for M16C/Tiny Series)
- M3062PT-80FPB [Discontinued]
Converter Board for 80-pin 0.65mm-pitch QFP (for M16C/60 Series)
- M30800T-PTC Converter for 100-pin 0.65mm-pitch LCC (for M16C family)
- M30290T-80FPD Converter Board for 80-pin 0.5-mm-pitch LQFP (for M16C/Tiny Series)
- M30291T-64FPD Converter Board for 64-pin 0.5-mm-pitch LQFP (for M16C/Tiny Series)
- M3T-100LCC-80QSB [Discontinued]
Converter from 100-pin 0.65mm-pitch LCC to 80-pin 0.65mm-pitch QFP (for M16C/60 Series)
- M3T-FLX-DCT613 [Discontinued]
Converter for Connecting 100-core Flexible Board FLX100 to M3T-DIRECT80S or M3T-FLX-80QSB (for M16C/60 Series)
- M30850T-EPBM [Discontinued]
MCU board for replacing the emulation probe M30850T-EPB (for M32C/80, 84, 85 and 86 Groups)
- M3062PT-EPBM [Discontinued]
MCU board for replacing the emulation probe M3062PT-EPB (for M16C/62P)

Converter for IC Packages : Exclusively for H8/300H Tiny Series

- R0E436049CFJ10 Converter board for 80pin 0.65mm pitch QFP (for H8/36049 Group)
- R0E436640CFG20 Converter Board for 64-pin 0.8-mm-pitch QFP
(for H8/3664, H8/3694, H8/3687, H8/36064, H8/36087 Group)
- R0E436640CFK20 Converter Board for 64-pin 0.5-mm-pitch LQFP
(for H8/3664, H8/3694, H8/3687, H8/3672, H8/36014, H8/36064, H8/36087 Group)

Converter for IC Packages : Exclusively for 740 Family 740 Series 75xx Group

- M37515T-PTC Converter for 64-core Flexible Board FLX64 (or M3T-64DIP-DMS) to 48-pin 0.5mm-pitch LQFP
(for 7515, 7516 Group)
- M37530T-PTC Converter for 42-pin 1.778mm-pitch SDIP to a 40-pin Narrow-pitch Connector
(for 7531, 7540, 7542, 7544 Group)
- M37530T-PTCB Converter for 40-pin Narrow-pitch Connector to 32-pin 0.8mm-pitch LQFP
(for 7531, 7532, 7534, 7540, 7542, 7544 Group)
- M37530T-PTCC Converter for 42-pin RSS Type Emulator MCU to 32-pin 1.778mm-pitch SDIP
(for 7531, 7540, 7542, 7544 Group)
- M37532T-PTC Converter for 42-pin 1.778mm-pitch SDIP to a 40-pin Narrow-pitch Connector (for 7532, 7534 Group)
- M3T-FLX-DCT503 [Discontinued] Board for Converting Pin Assignments to Connect the M37515T-RPD (for 7515 Group)

Converter for IC Packages : Exclusively for 740 Family

- M38007T-PRB Converter for 64-pin RSS Type Emulator MCU to 64-pin 0.5, 0.65 and 0.8mm-pitch QFP Target
- M38C29T-64FPD [Discontinued] Converter from 100-pin RFS Type Emulator MCU to 64-pin 0.5mm-pitch LQFP (for 38C1, 38C2, 38K0 and 38K2 Group of 38000 Series)
- M38C29T-64LCA [Discontinued] Converter from 100-pin RFS Type Emulator MCU to 64-pin 0.8mm-pitch QFP (for 38C1, 38C2, 38K0 and 38K2 Group of 38000 Series)
- M38D29T2-RLFS Emulator MCU board (for 38000 Series 38D2 Group)
- M38D29T2-RLFS-FP Emulator MCU board (for 38000 Series 38D2 Group)
- M38D29T2-RLFS-HP Emulator MCU board (for 38000 Series 38D2 Group)
- M3T-28DP-WS Converter for Connecting Emulator Probe to RSS Type MCU (for PC4701 system)
- M3T-28DP-WT Converter for Connecting Emulator Probe to RSS Type Emulator MCU (for PC4701 system/option)
- M3T-32LCC-A [Discontinued] Converter for Connecting Emulator Probe to RFS Type MCU (for PC4701 system/option)
- M3T-32LCC-S Converter for Connecting Emulator Probe to RFS Type MCU (for PC4701 system)
- M3T-42DIP-DMS [Discontinued] Converter for 42-pin RSS Type Emulator MCU to M3T-DCT42B-450 (or M3T-SSOP42B-450)
- M3T-64DIP-DMS Converter for 64-pin RSS Type Emulator MCU to M3T-DUMMY64
- PCA4625 Converter for 64-pin RSS Type Emulator MCU to 52-pin 1.778mm-pitch SDIP
- PCA4627 [Discontinued] Converter for 52-pin RSS Type Emulator MCU to 42-pin 1.778mm-pitch SDIP
- PCA4650G02 [Discontinued] Converter for Connecting Emulator Probe to RSS Type Emulator MCU (for PC4600 system)
- PCA4906 [Discontinued] Converter for 42-pin RSS Type Emulator MCU to 32-pin 1.778mm-pitch SDIP
- PCA4907 [Discontinued] Converter for 42-pin RSS Type Emulator MCU to 56-pin 0.8mm-pitch QFP
- PCA4912 [Discontinued] Converter for 42-pin RSS Type Emulator MCU to 32-pin 1.27mm-pitch SOP
- PCA4913 [Discontinued] Converter for 42-pin RSS Type Emulator MCU to 44-pin 0.8mm-pitch QFP
- PCA4933 Converter for Connecting Emulator Probe to RFS Type Emulator MCU (for PC4701, compact emulator, and PC4600 systems)
- M34282T5-OPT [Discontinued] MCU Board (for PC4400 Emulator System)

Converter for IC Packages : Exclusively for 4500 Series

- M34513T-PTCA Converter for Connecting 32-pin 1.778mm-pitch SDIP (for 4500 Series)
- M34513T-PTCB Converter for Connecting 32-pin 1.778mm-pitch SDIP to 40-core narrow-pitch (for 4500 Series)
- M34513T-PTCC Converter for Connecting 40-core narrow-pitch to 32-pin 0.8mm-pitch LQFP (for 4500 Series)
- M34553T-PTCA 50-pin Narrow-Pitch Connector Converter Board for M34552T2-CPE (for 4553, 4556 Group)
- M34553T-PTCB Converter Board for 48-pin 0.5-mm-pitch LQFP for M34552T2-CPE (for 4553 Group)

General-purpose Product (Pitch Converter Board)

- M3T-80P6-80P6S Converter for 80-pin 0.8mm-pitch LCC to 80-pin 0.65mm-pitch QFP
- M3T-100LCC-QSD Converter for 100-pin 0.65mm-pitch LCC to 100-pin 0.5mm-pitch LQFP
- M3T-64LCC-QSD Converter for 64-pin 0.8mm-pitch LCC to 64-pin 0.5mm-pitch LQFP
- M3T-80LCC-QSD Converter for 80-pin 0.8mm-pitch LCC to 80-pin 0.5mm-pitch QFP
- M3T-F160-100NRB Converter Board for Connecting FLX160 to 100-pin 0.65-mm-pitch QFP
- M3T-F160-100NSD Converter for 160-core Flexible Board FLX160 to 100-pin 0.5mm-pitch LQFP
- M3T-F160-100NSE Converter for 160-core Flexible Board FLX160 to 100-pin 0.4mm-pitch TQFP
- M3T-F160-128NRD Converter for 160-core Flexible Board FLX160 to 128-pin 0.5mm-pitch LQFP
- M3T-F160-80NRA Converter for 160-core Flexible Board FLX160 to 80-pin 0.5mm-pitch QFP/LQFP
- M3T-F160-80NSD Converter for 160-core Flexible Board FLX160 to 80-pin 0.5mm-pitch LQFP
- M3T-FLX-100LCC Converter for 100-core Flexible Board FLX100 to 100-pin 0.65mm-pitch LCC
- M3T-FLX-100NRB Converter for 100-core Flexible Board FLX100 to 100-pin 0.65mm-pitch QFP
- M3T-FLX-100NSD Converter for 100-core Flexible Board FLX100 to 100-pin 0.5mm-pitch LQFP
- M3T-FLX-100NSE Converter for 100-core Flexible Board FLX100 to 100-pin 0.4mm-pitch TQFP
- M3T-FLX-120NSE [Discontinued] Converter for Connecting 100-core Flexible Board FLX160 to 120-pin 0.4mm-pitch LQFP
- M3T-FLX-144NSD Converter for 160-core Flexible Board FLX160 to 144-pin 0.5mm-pitch LQFP
- M3T-FLX-144NSE Converter for 160-core Flexible Board FLX160 to 144-pin 0.4mm-pitch TQFP
- M3T-FLX-42SPB [Discontinued] Converter for 42-pin 1.778mm-pitch SDIP
- M3T-FLX-64NSA Converter for 100-core Flexible Board FLX100 to 64-pin 0.8mm-pitch QFP/LQFP
- M3T-FLX-80LCC [Discontinued] Converter for 100-core Flexible Board FLX100 to 80-pin 0.8mm-pitch LCC
- M3T-FLX-80NRA Converter for 100-core Flexible Board FLX100 to 80-pin 0.8mm-pitch QFP/LQFP
- M3T-FLX-80NSD Converter for 100-core Flexible Board FLX100 to 80-pin 0.5mm-pitch LQFP
- M3T-FLX-80QSB [Discontinued] Converter for 100-core Flexible Board FLX100 to 80-pin 0.65mm-pitch QFP
- PCA4687A Converter for 100-pin 0.65mm-pitch QFP to 100-pin 0.65mm-pitch LCC
- PCA4688A Converter for 80-pin 0.8mm-pitch QFP to 80-pin 0.8mm-pitch LCC
- PCA7759 MCU Signal Measurement Board for Renesas Emulator

General-purpose Product (for Height Adjustment)

- PCA4687B Converter for 100-pin 0.65mm-pitch LCC to 100-pin 0.65mm-pitch LCC (for Height Adjustment)
- PCA4688B Converter for 80-pin 0.8mm-pitch LCC to 80-pin 0.8mm-pitch LCC (for Height Adjustment)

General-purpose Product (for Direction Converting)

- M3T-FLX100-R Board for converting direction by 180°
- M3T-FLX100-T Board for converting direction by 90°
- M3T-FLX64-R Board for converting direction by 180°
- M3T-FLX64-T Board for converting direction by 90°

General-purpose Product (Dummy ICs and Related)

- M3T-100LCC-DMS [Discontinued] Converter for 100-pin 0.65mm-pitch LCC to M3T-DUMMY100S
- M3T-64LCC-DMS Converter for 64-pin 0.8mm-pitch LCC to M3T-DUMMY64
- M3T-80LCC-DMS Converter for 80-pin 0.8mm-pitch LCC to M3T-DUMMY80
- M3T-DCT42B-450 [Discontinued] Direct Dummy IC for 42-pin 0.8mm-pitch SSOP
- M3T-DIRECT100S [Discontinued] Direct Dummy IC for 100-pin 0.65mm-pitch QFP
- M3T-DIRECT80S [Discontinued] Direct Dummy IC for 80-pin 0.65mm-pitch SSOP
- M3T-DUMMY100S [Discontinued] Dummy IC for 100-pin 0.65mm-pitch QFP (100P6S-A, 100P6S-E)
- M3T-DUMMY64 [Discontinued] Dummy IC for 64-pin 0.8mm-pitch QFP (64P6N-A)
- M3T-DUMMY80 [Discontinued] Dummy IC for 80-pin 0.8mm-pitch QFP (80P6N-A)
- M3T-SSOP36B-450 [Discontinued] Direct Dummy IC for 36-pin 0.8mm-pitch SSOP
- M3T-SSOP42B-450 [Discontinued] Direct Dummy IC for 42-pin 0.8mm-pitch SSOP

Standard Pitch (2.54mm) Converter

- PCA4979 Converter from 80-pin 0.65mm-pitch QFP (80P6S-A) to 40-pin DIL Standard-pitch
- PCA4981A [Discontinued] Converter from 80-pin 0.8mm-pitch QFP (80P6-B) to 40-pin DIL Standard Pitch
- PCA4981B [Discontinued] Converter from 80-pin 0.8mm-pitch LCC (80D0) to 40-pin DIL Standard Pitch (with IC Socket)
- PCA4981C [Discontinued] Converter from 80-pin 0.8mm-pitch QFP (80P6N-A) to 40-pin DIL Standard Pitch
- PCA4988 Converter from 80-pin 0.8mm-pitch LCC (80D0) to 40-pin DIL Standard Pitch (with LCC Socket)
- PCA4989 [Discontinued]
Converter from 80-pin 0.65mm-pitch QFP (80P6S-A) to 40-pin DIL Standard Pitch (Different Pin Layout from the PCA4979)
- PCA7750G02 Converter board from 80-pin 0.8mm-pitch LCC (80D0) to 40-pin DIL Standard Pitch
(with LCC Socket and the Pattern for Oscillator)
- PCA7750G02-BARE [Discontinued]
Converter board from 80-pin 0.8mm-pitch QFP (80P6N-A) or LCC (80D0) to 40-pin DIL Standard Pitch
- PCA7752AG02 Converter board from 100-pin 0.65mm-pitch LCC (100D0) to 50-pin DIL Standard Pitch (with LCC Socket)
- PCA7752AG02-BARE [Discontinued]
Converter board from 100-pin 0.65mm-pitch QFP (100P6S-A) or LCC (100D0) to 50-pin DIL Standard Pitch
- PCA7752B Converter from 100-pin 0.65mm-pitch QFP (100P6S-A) to 50-pin DIL Standard Pitch
- PCA7754 Converter from 100-pin 0.5mm-pitch QFP (100P6Q-A) to 50-pin DIL Standard Pitch
- PCA7755A Converter from 64-pin 0.8mm-pitch QFP (64P6N-A) to 32-pin DIL Standard Pitch
- PCA7755B Converter from 64-pin 0.8mm-pitch LCC (64D0) to 32-pin DIL Standard Pitch
- PCA7755C Converter Board from 64-pin QFP (64P6Q) to 32-pin DIL Standard-Pitch (with QFP Socket and Pattern for Oscillator)
- PCA7755D Converter Board from 64-pin QFP (64P6U) to 32-pin DIL Standard-Pitch (with QFP Socket and Pattern for Oscillator)
- PCA7756 Converter from 80-pin 0.5mm-pitch QFP (80P6Q-A) to 40-pin DIL Standard Pitch
- PCA7757 Converter from 64-pin FLGA (64F0G) to 32-pin DIL Standard Pitch
- PCA7758 Converter from 36-pin 0.5mm-pitch QFN (36PJW-A) to 36-pin DIL Standard Pitch

Protection Board

- R0E330850ACBP0 Protection Board for M16C/60 Series M16C/62P Group and M32C/80 Series Emulator

Temporary Target Board

- M37450T-ADF Temporary Target Board for M37451RFS
- M37450T-ADS Temporary Target Board for M37451RSS
- M37531T-ADS Temporary Target Board for M37531RSS, M37532RSS, M37534RSS, M37536RSS, M37540RSS, M37542RSS and M37544RSS
- M38007T-ADS Temporary Target Board for M38007RSS, M38027RSS, M38049RLSS, M38117RSS, M38127RSS, M38807RSS, M38817RSS and M38887RSS
- M38067T-ADF Temporary Target Board for M38067RFS, M38078RFS, M38177RFS, M38207RFS, M38227RFS and M38867RFS
- M38187T-ADF Temporary Target Board for M38187RFS, M38197RFS, M38257RFS, M38267RLFS and M38277RFS
- M38517T-ADS Temporary Target Board for M38517RSS and M38507ARLSS
- M38C29T-ADF Temporary Target Board for M38C29RLFS
- M38C89T-ADF [Discontinued] Temporary Target Board for M38C89RLFS
- M38K29T-ADF Temporary Target Board for M38K09RFS, M38K29RFS

Oscillator Board

- OSC-2 Oscillator Board (Dumping Resistor Mounting Type)
- OSC-3 Oscillator Board (Oscillation Module Mounting Type)
- OSC-4 Oscillator Board (8 and 16MHz Selection Type)

Optional Cable

- M3T-F160-EXTC Extension Cable for FLX160
- R0E001000EXT00 External Trigger Cable for E100 Emulator
- R0E001000FLX00 Extension Flexible Cable for E100 Emulator

LCC Socket

- IC61-0644-052 64-pin LCC Socket (Manually Soldering Type) Made by Yamaichi Electronics Co., Ltd.
- IC61-0644-053 64-pin LCC Socket (Mounting Type) Made by Yamaichi Electronics Co., Ltd.
- IC61-0644-088 64-pin LCC Socket (Manually Soldering Type) Made by Yamaichi Electronics Co., Ltd.
- IC61-080-079 80-pin LCC Socket (Mounting Type) Made by Yamaichi Electronics Co., Ltd.
- IC61-080-081 80-pin LCC Socket (Manually Soldering Type) Made by Yamaichi Electronics Co., Ltd.
- IC61-0804-046 80-pin LCC Socket (Manually Soldering Type) Made by Yamaichi Electronics Co., Ltd.
- IC61-1004-051 100-pin LCC Socket (Manually Soldering Type) Made by Yamaichi Electronics Co., Ltd.