

























Microcontroller	Group	Product Name	Serial	USB	E1/E20	E2 Lite	E2	Select Product Name	Additional information
Renesas Synergy	S128	R7FS12878	✓ (TypeC)	-	-	-	-	Synergy	
Renesas Synergy	S1JA	R7FS1JA78	✓ (TypeC)	-	-	-	-	Synergy	
Renesas Synergy	S3A1	R7FS3A17C	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S3A3	R7FS3A37A	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S3A6	R7FS3A678	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S3A7	R7FS3A77C	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S5D3	R7FS5D37A	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S5D5	R7FS5D57A	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S5D5	R7FS5D57C	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S5D9	R7FS5D97C	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S5D9	R7FS5D97E	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S7G2	R7FS7G27G	✓ (TypeC)	✓	-	-	-	Synergy	
Renesas Synergy	S7G2	R7FS7G27H	✓ (TypeC)	✓	-	-	-	Synergy	
Power Management	Battery Management	RAJ240045	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
Power Management	Battery Management	RAJ240047	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
Power Management	Battery Management	RAJ240071	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
Power Management	Battery Management	RAJ240075	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
Power Management	Battery Management	RAJ240080	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
Power Management	Battery Management	RAJ240090	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
Power Management	Battery Management	RAJ240100	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
Power Management	Battery Management	RAJ240500	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
Renesas USB Power Delivery	C30	R9A02G011	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
Renesas USB Power Delivery	C30	R9J02G012	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	
ICs for Motor Driver/Actuator Driver	ICs for Motor Control	RAJ306000	✓ (TypeB)	-	✓ (1 wire UART)	✓ (1 wire UART)	✓ (1 wire UART)	RL78	