


NOTES:
 All dimensions and coordinates are in microns. Coordinates are referenced to the geometric center of the die.

PAD DIMENSIONS		
TYPE	X	Y
A	120	120
B	184	120
C	248	120

REV	DCN NO.	APPROVAL/DATE	 Integrated Device Technology, Inc. 2972 Stender Way, Santa Clara, CA, 95051 (408) 727-6116 FAX: (408) 727-2328
00	23965	T.G. 8/18/94	
01	30073	<i>[Signature]</i> 2-21-95	
FEB 24 1995			72104 Y 4096 X 9-BIT CONFIGURABLE PARALLEL/SERIAL FIFO
DIE SIZE:		DRAWING NO.	
5538 um x 6620 um		PSC-4512	
Thickness: 0.020"		SHEET 1 OF 2	

PAD #	NAME	X	Y	TYPE
1	/W	-179.06	3074.79	A
2	D4	-697.44	3074.79	A
3	D3	-1216.24	3074.79	A
4	D2	-1569.23	3074.79	A
5	D1	-2169.23	3074.79	A
6	N/C	-2582.05	3074.79	A
7	D0	-2586.33	2568.38	A
8	/XI	-2586.33	2102.97	A
9	/SO,PO	-2586.33	838.46	A
10	SOX	-2586.33	363.68	A
11	SOCP	-2586.33	-147.86	A
12	SO	-2586.33	-712.82	A
13	/AEF	-2586.33	-1075.64	A
14	/FF-1	-2586.33	-1577.35	A
15	/FF	-2586.33	-2041.45	A
16	Q0	-2586.33	-2594.44	A
17	N/C	-2582.05	-3075.21	A
18	Q1	-2168.38	-3075.21	A
19	Q2	-1444.44	-3075.21	A
20	Q3	-1048.72	-3075.21	A
21	Q4	-487.18	-3075.21	A
22	GND	-238.89	-3064.53	A
23	GND	-55.13	-3064.53	A
24	GND	128.63	-3064.96	A
25	/R	408.97	-3075.21	A
26	Q5	779.06	-3075.21	A

PAD #	NAME	X	Y	TYPE
27	Q6	1280.77	3075.21	A
28	Q7	1727.78	3075.21	A
29	Q8	2229.49	3075.21	A
30	N/C	2581.62	3075.21	A
31	/XO,/HF	2585.9	-2556.41	A
32	/EF	2585.9	-2054.7	A
33	/EF+1	2585.9	-1676.07	A
34	/OE	2585.9	-1109.83	A
35	/SI,/PI	2585.9	190.17	A
36	SIX	2585.9	660.68	A
37	SICP	2585.9	1170.94	A
38	SI	2585.9	1638.46	A
39	/RS	2585.9	2106.41	A
40	/FL,/RT	2585.9	2591.88	A
41	N/C	2581.62	3074.79	A
42	D8	2250	3075	A
43	D7	1679.06	3075	A
44	D6	1284.19	3075	A
45	D5	791.03	3075	A
46	VCC	439.53	3075	C
47	VCC	-142.74	3074.79	B

FEB 24 1995

REV	DCN NO.	APPROVAL / DATE	Integrated Device Technology, Inc. 2972 Stender Way, Santa Clara, Ca. 95051 (408) 727-6116 FAX: (408) 727-2328			
OO	23965	T. GALLOWAY 8/18/94			72104 Y 4096 x 9-BIT CONFIGURABLE PARALLEL/SERIAL FIFO	
O1	30073	<i>TG</i> 2-21-95				
			DIE SIZE: 5538 um x 6620 um	DRAWING NO. PSC-4512		
			THICKNESS: 0.020"	SHEET 2 OF 2		