

# TIMING OVERVIEW SOLUTIONS

Industry's broadest and deepest timing portfolio



Renesas offers the broadest and deepest silicon timing portfolio in the industry. In addition to our wide selection of buffers, oscillators, and clock synthesizer products, we deliver leading-edge system timing solutions to resolve timing challenges in virtually any applications. With proven expertise spanning more than twenty years in both analog and digital timing, our portfolio features the lowest phase noise and highest performance advanced timing technology.

## Renesas timing features

- Lowest phase noise and highest performance
- Industry's broadest and deepest portfolio
- Proven expertise in both analog and digital timing
- Advanced timing technology

## Renesas timing benefits

- Extensive online tools library
- Deep knowledge base / FAQ
- Expert engineering support

## Applications

- Wireless infrastructure
- Networking
- Datacenters
- Consumer electronics
- Industrial systems
- Automotive infotainment and navigation

## APPLICATION-SPECIFIC AND REAL-TIME CLOCKS

### Application-Specific Clocks

Meeting Industry Standards

Renesas' wide variety of application-specific clocks provides engineers with targeted solutions to simplify their design process. These devices are optimized for specific requirements so perform better and are easier to use in target applications than general-purpose clocking parts. We offer a full portfolio of clock generation and distribution products designed specifically for:

- Network Synchronization, IEEE 1588, Synchronous Ethernet
- PCI Express
- RF and JESD204B
- Spread Spectrum clocks
- Processor clocks

To learn more, visit [renesas.com/app\\_clocks](https://renesas.com/app_clocks)

### Real-Time Clocks


Renesas' real-time clock ICs are ultra-low-power clock/date devices with programmable time-of-day alarms and programmable square-wave outputs. High noise immunity, low current consumption, 12 / 24 hour operation modes, leap year auto correction, and programmable square wave output make them ideal for a wide range of design applications.

Our RTCs count seconds, minutes, hours, day, date, month, and year with leap-year compensation valid up to 2100 and feature:

- Normal and fast-mode I2C interfaces
- Two time-of-day alarms
- Oscillator stop flag
- Operating voltage range from 1.8 – 5.5V

To learn more, visit [renesas.com/rtc](https://renesas.com/rtc)

## CLOCK GENERATORS



- General purpose solutions
- Low and ultra-low jitter families
- Extreme performance products
- Flexible programmable clocks


### Industry's most comprehensive portfolio of ultra-flexible programmable timing devices

Widely recognized as the industry's most comprehensive portfolio of ultra-flexible, programmable timing devices, Renesas clock synthesizers are all PLL clock-based products that generate one or more clock signals within an application. Our clock generators and frequency synthesizers can generate different output frequencies from a common input frequency, satisfying complex clocking system requirement needs.

Renesas' products produce clock output frequencies within strict tolerances for the application they are clocking and allow for frequency translation – either multiplication or division. We also offer solutions for single-ended and differential clock outputs, as well as devices with an external feedback path for more precise control.

To learn more, visit [renesas.com/clockgen](https://renesas.com/clockgen)

## CLOCK DISTRIBUTION



- Clock dividers and fanout buffers
- Zero delay buffers
- Multiplexers and fanout multiplexers


Renesas clock distribution products are used to condition, manipulate and distribute clock signals within a system, with or without the use of a PLL. These devices are well-suited for most applications where the input signal is of good quality and the goal is to buffer, fanout, divide, or multiplex the input signal. A single-output clock buffer is also useful for translating a clock from one signaling standard to another, such as LVCMOS-in to LVPECL-out.

Our rich portfolio of clock buffer, distribution and multiplexer solutions meets your needs for virtually any application. With the industry's largest portfolio of clock distribution devices supporting differential signals, common I/O levels supported by these devices include LVDS, LVPECL, HCSSL, LVCMOS, CML, HSTL, and SSTL.

Renesas Advantages:

- Broad portfolio – Industry-leading coverage for all market segments
- Strong performance – Best in class combination of skew (<35 ps), jitter (<50 fs) and power (30 mA for 4 outputs)
- Flexible designs – Pin-selectable output type and I<sup>2</sup>C programmable families
- Robust – Available in commercial and industrial temperature ranges
- Space-saving devices – Small packages and integrated input termination networks for differential signals

To learn more, visit [renesas.com/buffers](https://renesas.com/buffers)



## JITTER ATTENUATORS




Renesas' jitter attenuators remove unwanted noise from one or more input clock signals. Integrating a jitter attenuator and frequency translator simplifies the circuit and minimizes the BOM for your designs.

Universal frequency translator (UFT) family offers:

- Translations from virtually any input frequency to any output frequency
- Eight independently programmable clocking outputs
- Flexibility to generate eight different frequencies in up to four frequency domains

To learn more, visit [renesas.com/ja](https://renesas.com/ja)

## OSCILLATORS



### Quartz Crystal Oscillator ICs (XO), Crystal Clock Oscillators, and Low Power Oscillator Circuits

Renesas offers XO's and FemtoClock™ NG programmable oscillator ICs to meet your needs in virtually any application.

- High-performance, low-jitter XL and XU crystal oscillators
  - Various frequency, performance level, output, package, and temp options
  - AEC-Q200 Automotive-grade XA family

To learn more, visit [renesas.com/xo](https://renesas.com/xo)

## DESIGN RESOURCES

### Timing Commander™ Software

Renesas' Timing Commander™ is a simple configuration tool for complex timing solutions. This innovative Windows™-based software platform enables system design engineers to configure, program, and monitor sophisticated timing devices with an intuitive and flexible GUI. Timing Commander empowers your customers to expedite their development cycles and optimize the configuration of our industry-leading clocking solutions.

Help your customers get command of their timing tree and easily:

- Configure, program, and monitor sophisticated timing devices
- Create phase noise plots
- Generate schematic symbols and termination circuits
- Calculate estimated power consumption

To learn more, visit [renesas.com/timingcommander](https://renesas.com/timingcommander)

### Renesas IC Toolbox (RICBox)

The Renesas IC Toolbox (RICBox) software platform enables customers to configure Renesas devices on evaluation kits. The platform also enables customers to construct profiles for devices with non-volatile memory, important for clock devices that need to power on in their desired configuration during system start up.

- Supports OTP and EEPROM burning
- Installation and updates accessible on the cloud
- Graphical Status Monitoring
- Pre-loaded reference designs
- Algorithms for optimizing loop filters

To learn more, visit [renesas.com/ricbox](https://renesas.com/ricbox)

To request samples, download documentation or learn more visit: [renesas.com/timing](https://renesas.com/timing)



Renesas Electronics America Inc. | [renesas.com](https://renesas.com)  
1001 Murphy Ranch Road, Milpitas, CA 95035 | Phone: 1-888-468-3774

© 2023 Renesas Electronics America Inc. (REA). All rights reserved. All trademarks are the property of their respective owners. REA believes the information herein was accurate when given but assumes no risk as to its quality or use. All information is provided as-is without warranties of any kind, whether express, implied, statutory, or arising from course of dealing, usage, or trade practice, including without limitation as to merchantability, fitness for a particular purpose, or non-infringement. REA shall not be liable for any direct, indirect, special, consequential, incidental, or other damages whatsoever, arising from use of or reliance on the information herein, if advised of the possibility of such damages. REA reserves the right, without notice, to discontinue products or make changes to the design or specifications of its products or other information herein. All contents are protected by U.S. and international copyright laws. Except as specifically permitted herein, no portion of this material may be reproduced in any form, or by any means, without prior written permission from Renesas Electronics America Inc. Visitors or users are not permitted to modify, distribute, publish, transmit or create derivative works of any of this material for any public or commercial purposes.

Document No.: R31DS0005EU0001