

R-IN32M3-EC/CL

R18AN0039EJ0126

Rev.1.26

Driver/Middleware Set for R-IN32M3-EC/CL Release Note

Dec 27, 2018

Summary

This document describes the package contents and operating environment of this product.

Please be sure to read before use.

For details on how to use each sample software, middleware etc, please refer to the related documents below.

Related documents

R18UZ0003EJ****	R-IN32M3-EC User's Manual
R18UZ0005EJ****	R-IN32M3-CL User's Manual
R18UZ0024EJ****	R-IN32M3-CL Development Tools Startup Manual
R18UZ0011EJ****	R-IN32M3 Series Programming Manual (OS edition)
R18UZ0021EJ****	R-IN32M3 Series User's Manual (Board design edition)
R18UZ0009EJ****	R-IN32M3 Series Programming Manual (Driver edition)
R18UZ0007EJ****	R-IN32M3 Series User's Manual Peripheral Functions
R18UZ0056EJ****	R-IN32 Series User's Manual CC-Link remote device station

Last four digits of document number (described as ****) indicate version information of each document.

Please download the latest document from our web site and refer to it.

Contents

1. Introduction	2
2. Package Contents	2
3. Folder structure.....	2
4. Operating environment.....	3
5. Website and Support.....	4

1. Introduction

CC-Link remote device station package for R-IN32M3-EC/-CL is a software package that summarizes the sample applications of CC-Link remote device stations Ver 1 and Ver 2 using RIN32m3-EC/CL.

This package is used in combination with driver and middleware package. please move CCSV 1 / CCSV 2 of this package to the \ Project of middleware / driver and use it.

2. Package Contents

The sample applications, libraries, middleware, and peripheral function drivers included in this package are shown below.

- Sample application

No.	Sample application name
1	CC-Link Ver.1 for sample application
2	CC-Link Ver.2 for sample application

3. Folder structure

Folder structure of this package is shown below.

TOP

```

|
+-- CCSV1    <-- CC-Link Version 1
|   +-- readme.txt
|   +-- ARM
|   +-- GCC
|   +-- GX_works2  【Sample Project File for GX Works2】
|   +-- IAR
|
+-- CCSV2    <-- CC-Link version 2
|   +-- readme.txt
|   +-- ARM
|   +-- GCC
|   +-- GX_works2  【Sample Project File for GX Works2】
|   +-- IAR

```

4. Operating environment

The operating environment of this package is shown below.

- Target device
 - R-IN32M3-EC
 - R-IN32M3-CL

- Target board
 - R-IN32M3-EC TESSERA Board (TS-R-IN32M3-EC)
 - R-IN32M3-CL TESSERA Board (TS-R-IN32M3-CL)

- Development environment
 - Compiler
 - IAR Embedded Workbench for ARM 7.80
 - Debugger
 - IAR Embedded Workbench for ARM 7.80
 - ICE
 - I-jet / JTAGjet-Trace (IAR)

5. Website and Support

Renesas Electronics Website

<http://www.renesas.com/>

Inquiries

<http://www.renesas.com/contact/>

All trademarks and registered trademarks are the property of their respective owners.

Change history

Version	Changes
V1.2.6 (2018/11/19)	[Changed] /CCSV1/main.c /CCSV2/main.c - IOTENSU changed to low fixed. "Number of I/O points fixed to 32 points" can not be used.
V1.2.5 (2017/12/12)	[Add] - Added RUN LED on / off control by master station version. - RUN LED off when the master station is Ver.1 - RUN LED on when the master station is other than Ver.1 - RUN LED turns off when communication timeout occurs. - Added initialization port setting for RUN LED control.

<p>V1.2.4 (2015/11/30)</p>	<p>The following type name of products correspond with "Revision 2" and the other type name of products with "Revision 1"</p> <ul style="list-style-type: none"> - Revision 2 R-IN32M3-EC : MC-10287BF1-HN4-M1-A / MC-10287BF1-HN4-A R-IN32M3-CL : UPD60510BF1-HN4-A / UPD60510BF1-HN4-M1-A <p>[Changed]</p> <p>/CCSV1/IAR/boot_norflash.icf /CCSV1/IAR/boot_serialflash.icf /CCSV1/IAR/iram.icf /CCSV1/ARM/scat_boot_extrom.ld /CCSV1/ARM/scat_boot_iram.ld /CCSV1/ARM/scat_boot_sflash.ld /CCSV1/GCC/scat_boot_extrom.ld /CCSV1/GCC/scat_boot_iram.ld /CCSV1/GCC/scat_boot_sflash.ld</p> <p>/CCSV2/IAR/boot_norflash.icf /CCSV2/IAR/boot_serialflash.icf /CCSV2/IAR/iram.icf /CCSV2/ARM/scat_boot_extrom.ld /CCSV2/ARM/scat_boot_iram.ld /CCSV2/ARM/scat_boot_sflash.ld /CCSV2/GCC/scat_boot_extrom.ld /CCSV2/GCC/scat_boot_iram.ld /CCSV2/GCC/scat_boot_sflash.ld</p> <p>There are two types of mapping files and startup routines in this sample software. One is for "Revision 1" (CPU access area limitation *notice) The other is for "Revision 2" (no limitation)</p> <p>Mapping file(*.ld) and startup routine (startup_RIN32M3.c) for ARM are updated. Before: The common area is assigned for stack and Heap. After: Dedicated area is assigned for Heap. Especially GCC, please use mapping file and startup routine for same Revision.</p> <p>Mapping file for Revision 1 r-in32m3_samplesoft/Device/Renesas/RIN32M3/Source/Templates/IAR/rev1 r-in32m3_samplesoft/Device/Renesas/RIN32M3/Source/Templates/GCC/rev1 r-in32m3_samplesoft/Device/Renesas/RIN32M3/Source/Templates/ARM/rev1</p> <p>Mapping file for Revision 2 r-in32m3_samplesoft/Device/Renesas/RIN32M3/Source/Templates/IAR/rev2 r-in32m3_samplesoft/Device/Renesas/RIN32M3/Source/Templates/GCC/rev2 r-in32m3_samplesoft/Device/Renesas/RIN32M3/Source/Templates/ARM/rev2</p> <p>*notice Please refer below documentation http://documentation.renesas.com/doc/products/mpumcu/tu/tnrina001be.pdf</p>
<p>V1.2.3 (2015/8/31)</p>	<p>[Changed]</p> <p>/CCSV1/GCC/scat_boot_iram.ld /CCSV2/GCC/scat_boot_iram.ld</p> <ul style="list-style-type: none"> - Remove unnecessary definition of linker file.

V1.2.2 (2015/5/19)	<p>[Changed]</p> <ul style="list-style-type: none"> - Update EWARM project file and makefiles. - Change the processing of timeout setting function. - "RIN32M3_CL" is defined.
V1.2.1 (2015/2/13)	<p>[Add]</p> <ul style="list-style-type: none"> - Add port setting for R-IN32M3-EC Evaluation Board. - Add sample code for bidirectional communication. <p>[Changed]</p> <ul style="list-style-type: none"> - Change interrupt port to INTPZ7 in CCSV2.
V1.2.0 (2015/1/23)	<p>[Changed]</p> <p>Correspondence of Conformance Test</p> <ul style="list-style-type: none"> - Additional application buffer - Disable loopback function (initial state)
V1.1.0 (2014/1/16)	<p>[Fixed]</p> <ul style="list-style-type: none"> - Fix how to monitor INTPZ1 pin in CCSV2. - Fix port control for RS-485 transceiver. <p>[Changed]</p> <ul style="list-style-type: none"> - Update EWARM project file and makefiles. - Delete CC-Link IE WDT disable sequence. - Port setting sequences.
V1.0.0 (2016/1/29)	<p>First release</p>

General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Handling of Unused Pins

Handle unused pins in accordance with the directions given under Handling of Unused Pins in the manual.

- The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.

2. Processing at Power-on

The state of the product is undefined at the moment when power is supplied.

- The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.

In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.

In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

3. Prohibition of Access to Reserved Addresses

Access to reserved addresses is prohibited.

- The reserved addresses are provided for the possible future expansion of functions. Do not access these addresses; the correct operation of LSI is not guaranteed if they are accessed.

4. Clock Signals

After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.

- When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.

5. Differences between Products

Before changing from one product to another, i.e. to a product with a different part number, confirm that the change will not lead to problems.

- The characteristics of Microprocessing unit or Microcontroller unit products in the same group but having a different part number may differ in terms of the internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

- Arm[®] and Cortex[®] are registered trademarks of Arm Limited (or its subsidiaries) in the EU and/or elsewhere. All rights reserved.
- Ethernet is a registered trademark of Fuji Xerox Co., Ltd.
- IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers Inc
- TRON is an acronym for "The Real-time Operation system Nucleus.
- ITRON is an acronym for "Industrial TRON.
- μ ITRON is an acronym for "Micro Industrial TRON.
- TRON, ITRON, and μ ITRON do not refer to any specific product or products.
- CC-Link and CC-Link IE Field are registered trademarks of the CC-Link Partner Association (CLPA).
- Additionally all product names and service names in this document are a trademark or a registered trademark which belongs to the respective owners.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics Corporation

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan

Renesas Electronics America Inc.

1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited

9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.

Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.

Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited

Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852 2886-9022

Renesas Electronics Taiwan Co., Ltd.

13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.

80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.

Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.

No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.

17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338