NX6510GH

RENESAS

LASER DIODE 1 550 nm InGaAsP MQW-DFB LASER DIODE FOR 1.25 Gb/s FTTH P2P AND OC-48 IR-2

DESCRIPTION

The NX6510GH is a 1 550 nm Multiple Quantum Well (MQW) structured Distributed Feed-Back (DFB) laser diode with InGaAs monitor PIN-PD.

APPLICATIONS

- 1.25 Gb/s FTTH P2P
- OC-48 IR-2

FEATURES

- Optical output power
- Low threshold current
- Differential efficiency
- Wide operating temperature range
- InGaAs monitor PIN-PD
- CAN package
- Focal point

- $P_{0} = 5.0 \text{ mW}$ $I_{th} = 10 \text{ mA}$
- $\eta_{\rm d} = 0.35 ~{\rm W/A}$
- $T_{\rm C} = -40$ to $+85^{\circ}{\rm C}$


\phi 5.6 mm 7.5 mm





R08DS0051EJ0100 Rev.1.00 Jan 19, 2012

PACKAGE DIMENSIONS (UNIT: mm)





ORDERING INFORMATION

Part Number	Package	Pin Connections
NX6510GH	4-pin CAN with aspherical lens cap	

Remarks 1. The color of lens cap might be observed differently.

2. The hermetic test will be performed as AQL 1.0%.




ABSOLUTE MAXIMUM RATINGS ($T_A = 25^{\circ}C$, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Optical Output Power	Po	10	mW
Forward Current of LD	IF	150	mA
Reverse Voltage of LD	V _R	2.0	V
Forward Current of PD	IF	10.0	mA
Reverse Voltage of PD	V _R	15	V
Operating Case Temperature	Tc	–40 to +85	°C
Storage Temperature	T _{stg}	–40 to +85	°C
Lead Soldering Temperature	T _{sld}	350 (3 sec.)	°C
Relative Humidity (noncondensing)	RH	85	%

ELECTRO-OPTICAL CHARACTERISTICS (T_c = 25°C, CW, BOL, unless otherwise specified)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Optical Output Power	Po		-	5.0	-	mW
Operating Voltage	V _{op}	P_0 = 5.0 mW, T_c = -40 to 85°C	- (1.1	1.6	V
Threshold Current	I _{th}		-	10	20	mA
		T _c = -40 to 85°C			50	
Differential Efficiency	η_{d}	P _o = 5.0 mW	0.20	0.35	-	W/A
		P _o = 5.0 mW, T _{c =} –40 to 85°C	0.10	_	-	W/A
Peak Emission Wavelength	λρ	P_0 = 5.0 mW, $T_c = -40$ to $85^{\circ}C$	1 530	-	1 570	nm
Side Mode Suppression Ratio	SMSR	P _O = 5.0 mW, T _{C =} -40 to 85°C	30	-	_	dB
Rise Time	tr	$I_{b} = I_{th}, 20-80\% P_{O} = 5.0 \text{ mW}$	_	100	150	ps
Fall Time	t _f	I _b = I _{th} , 80-20% P _O = 5.0 mW	_	100	150	ps
Monitor Current	I _m	V _R = 1.5 V, P _O = 5.0 mW	80	-	1 200	μA
Monitor Dark Current	I _D	$V_{R} = 5 V, T_{C} = -40 \text{ to } 85^{\circ}C$	_	-	100	nA
Monitor PD Terminal	Ct	V _R = 5 V	_	-	20	pF
Capacitance						
Tracking Error *1	γ	$T_{C} = -40$ to $85^{\circ}C$, $I_{m} = const.$	-1.0	-	1.0	dB
		(@ P _o = 5.0 mW, T _c = 25°C)				

Note: 1. Tracking Error: γ





SAFETY INFORMATION ON THIS PRODUCT



SEMICONDUCTOR LASER

AVOID EXPOSURE-Invisible Laser Radiation is emitted from this aperture

Warning Laser Beam	A laser beam is emitted from this diode during operation. The laser beam, visible or invisible, directly or indirectly, may cause injury to the eye or loss of eyesight.
	Do not look directly into the laser beam.
	Avoid exposure to the laser beam, any reflected or collimated beam.
Caution GaAs Products	This product uses gallium arsenide (GaAs). GaAs vapor and powder are hazardous to human health if inhaled or ingested, so please observe the following points.
	• Follow related laws and ordinances when disposing of the product. If there are no applicable laws and/or ordinances, dispose of the product as recommended below.
	 Commission a disposal company able to (with a license to) collect, transport and dispose of materials that contain arsenic and other such industrial waste materials.
	2. Exclude the product from general industrial waste and household garbage, and ensure that the product is controlled (as industrial waste subject to special control) up until final disposal.
	• Do not burn, destroy, cut, crush, or chemically dissolve the product.
	• Do not lick the product or in any way allow it to enter the mouth.



		Description		
Rev.	Date	Page	Summary	
1.00	Jan 19, 2012	-	First edition issued	

Notice

- All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renease Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renease Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics
- assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Re
 depends on the product's quality grade as indicated below. You must check the quality grades: "Standard", "High Quality", and "Specific".
- depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the prior written consent of Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 "Standard" Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic applicace; machine tools;
- "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine personal electronic equipment; and industrial robots.
- "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
- *Specific*: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and maffunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and maffunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.

ronics

- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Ele
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

s Ele

Refer to "http://www.renessas.dom" for the latest and detailed information.

Renesas Electronics America Inc.
2880 Scott Boulevard Santa Clara, CA 93050-2554, U.S.A.
Tel: +14095-688-6000, Fast, +1408-588-6130

Renesas Electronics Canada Limited
1101 Nicholson Road, Newmarket, Ortario L3Y 9C3, Canada
Tel: +1-905,688-6401, Fast, +1409-588-8130

Renesas Electronics Curope Limited
Dukes Meadow, Millobard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +440628-565-100, Fast, +44-1628-585-900
Renesas Electronics Europe Limited
Tai: 44-1628-565-100, Fast, +44-1628-568-900
Renesas Electronics Curope Limited
Tai: 44-1628-565-100, Fast, +44-1628-568-900
Renesas Electronics Curope CombH
Accadiestrases 10, 40472 Disseldorf, Gernany
Tel: +44-1628-565-100, Fast, +46-218-563-1327
Renesas Electronics (China) Co., Ltd.
Thi Floor, Nountom Plaza, No.e7 ZhilchunLu Haidian District, Beijing 100083, P.R.China
Tel: +46-10-8235-1155, Fast, +86-10-8235-7679
Renesas Electronics (China) Co., Ltd.
Unit 204, 205, AZIA Conter, No.1233 Luijazui fing Rd., Pudong District, Shanghai 200120, China
Tel: +86-21-587-718 J, Fax: +86-221-6867-7858 / 7898
Renesas Electronics Taiwan Co., Ltd.
Unit 204, 205, AZIA Conter, No.1233 Luijazui fing Rd., Pudong District, Shanghai 200120, China
Tel: +86-21-586-507, Teste +85-22866-52790
Renesas Electronics Taiwan Co., Ltd.
Unit 204, 205, AZIA Conter, No.1233 Luijazui fing Rd., Pudong District, Shanghai 200120, China
Tel: +86-24-587-7058 / 78980
Renesas Electronics Taiwan Co., Ltd.
Unit 204, 205, AZIA Conter, No.1233 Luijazui fing Rd., Pudong District, Shanghai 200120, China
Tel: +86-24-587-507, Teste +86-2286-527904
Renesas Electronics Taiwan Co., Ltd.
Tif: -No.7865-5910, Career 20229044
Renesas Electronics Singapore Ple. Ltd.
Thanburfront Annue, #66-10, Keppel Bay Tower, Singapore 098632
Tel: +80-24-587-500, Fax: +88-2486-24875-9670
Renesas Electronics Kingapore Ple. Ltd.
Thanburfront Annue, #66-10, Keppel Bay Tower, Singapore 098632
Tel: +80-2795-9300, Fax: +80-2479-8071
Renesas Electronics Kingapore Ple